

# PHILIPS

Bulb

LED

14W-100W

E27

Warm/Extra Warm/Very Warm

Non-dimmable



8718696706794



## One lamp. Your switch. Three light settings.

Change your room ambience to suit whatever you're doing. With the Philips SceneSwitch LED lamp, you can easily change the setting from bright light, to natural light and to a cosy warm glow. All you need is your existing switch.

### Choose for a sustainable solution

- Long-life bulbs – Last up to 15 years

### Light beyond illumination

- Restore the lamp to the default factory setting
- No dimmer or additional installation needed
- The lamp can memorise your last setting

# Highlights

## 15,000-hour rated average life



With a lifetime of up to 15,000 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 15 years.

## Plug and play



Does not require any additional installation or a dimmer switch. This lamp is not suitable for use with dimmers. If used on a dimmer setting, the dimmer is set to 100% brightness.

## Auto memory (sceneswitch)



This Scene Switch lamp has a built-in memory chip which will memorise your last light setting if the switch is turned off for longer than 6 seconds. If you don't often switch between activities, the light will be in your favourite mode when you turn it on again.

## Reset (Sceneswitch)



If multiple lamps are used and they are no longer synchronised, simply toggle the switch (turn it on and off again within 1 second) to restore the lamps to the default factory setting.

# Specifications

## Characteristics

- Shape: Bulb
- Dimmable: No
- Lamp shape: Non-directional bulb
- Socket: E27

## Durability

- Average life (at 2.7 hrs/day): 15 a
- Lumen maintenance factor: 0.7
- Nominal lifetime: 15,000 h
- Number of switch cycles: 100,000

## Lamp dimensions

- Height: 13.91 cm
- Width: 7.11 cm

**Light characteristics**

- Beam angle: 150 degree(s)
- Colour rendering index (CRI): 80
- Colour temperature: 2700–2500–2200 K
- Light Colour Category: Warm/Very Warm/Extra Warm
- Nominal luminous flux: 1521–600–150 lm
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light

**Miscellaneous**

- EyeComfort: Yes

**Other characteristics**

- Lamp Classification Risk Group: RG1
- Lamp current: 135 mA

**Packaging information**

- Product family: LED Classic, EyeComfort

**Power consumption**

- Power factor: 0.5
- Voltage: 220–240 V
- Wattage: 14, 7, 3.5 W
- Wattage equivalent: 100 W
- Energy efficiency label (EEL): A+

**Product dimensions and weight**

- Length: 13.91 cm

**Rated values**

- Rated beam angle: 150 degree(s)
- Rated lifetime: 15,000 h
- Rated luminous flux: 1521–600–150 lm
- Rated power: 14–7–3.5 W

**Technical specifications**

- Frequency: 50–60 Hz



Issue date: 2023-11-08  
Version: 0.694

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)