

PHILIPS

Spot

LED

1.5-3.5-5W (5-20-50W)

GU10

Non-dimmable



8718696710937



Switch light settings without switching bulbs

Sometimes you feel like a change in ambiance to suit whatever you're doing. With a Philips SceneSwitch LED spot, you can easily change the setting with your existing switch. No dimmer or additional installation is required.

High-quality light

- Learn about light
- Designed for the comfort of your eyes

Choose for a sustainable solution

- No UV or InfraRed
- Long-life bulbs – Last up to 15 years
- Better for your wallet and your planet

Create the right light for your home

- Perfect for accent lighting

Light beyond illumination

- Three light settings from 2700 K to 2500 K to 2200 K
- The lamp can memorise your last setting
- Restore the lamp to the default factory setting

Highlights

Learn about light



Colour temperature: light can have different colour temperatures, indicated in units called Kelvin (K). Lamps with a low Kelvin value produce a warm, more tranquil light, while those with a higher Kelvin value produce a cool, more energising light. CRI: the colour rendering index (CRI) is used to describe the effect of a light source on colour appearance. Natural sunlight has a CRI of 100. The CRI of Philips LED lamps is always higher than 80, which ensures that colours are shown as true and natural.

Gentle LEDs, easy on the eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

No UV or IR




The light has no infra-red component, so no heat is radiated. Also, there is no ultra-violet component in this light. These two characteristics mean that this light will not cause fabric and other items to fade.

15,000-hour rated average life



With a lifetime of up to 15,000 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 15 years.

Saves up to 80% energy



LED technology saves up to 80% energy compared to your standard bulb. It therefore pays for itself and saves you money year after year. It also helps to protect the environment.

Perfect for accent lighting



Modern lighting with a familiar wide-angle light output (36 degrees), this LED spot is suitable for both accent lighting and general-purpose lighting. It can be used in recesses and track light fixtures, and is ideal for use in kitchens, kitchen island lighting, living rooms and dining rooms.

Three light settings

Light can have different colour temperatures, indicated in units called Kelvin (K). Bulbs with a low Kelvin value produce a warm, cosy light, while those with a higher Kelvin value produce a more energising light. These new Scene Switch bulbs allow you to switch from functional lighting to natural light and to a cosy, warm dimmed light. Light levels can change from 100% to 40% to 10%. Now you can easily customise your room for a variety of tasks or adapt it to suit your mood.

Auto memory (sceneswitch)

This Scene Switch lamp has a built-in memory chip which will memorise your

last light setting if the switch is turned off for longer than 6 seconds. If you don't often switch between activities, the light will be in your favourite mode when you turn it on again.

Reset (Sceneswitch)

If multiple lamps are used and they are no longer synchronised, simply toggle the switch (turn it on and off again within 1 second) to restore the lamps to the default factory setting.

Specifications

Characteristics

- Dimmable: No
- Intended use: Indoor
- Lamp shape: Directional reflector
- Socket: GU10
- Technology: LED

Lamp dimensions

- Height: 5.4 cm
- Weight: 0.054 kg
- Width: 5 cm

Durability

- Average life (at 2.7 hrs/day): 15 a
- Lumen maintenance factor: 70%
- Nominal lifetime: 15,000 h
- Number of switch cycles: 50,000

Light characteristics

- Beam angle: 36 degree(s)
- Colour consistency: 6SDCM
- Colour rendering index (CRI): 80
- Colour temperature: 2200-2500-2700 K
- Light Colour Category: Warm/Extra Warm/Very Warm
- Nominal luminous flux: 345 lm
- Warm-up time to 60% light: Instant full light

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Lamp current: 43 mA
- Efficacy: 69 lm/W

Packaging information

- EAN: 8718696710937
- EOC: 871869671093701
- Product title: LED SSW 50W GU10 WW 36D ND SRT4

Power consumption

- Power factor: 0.5
- Voltage: 220-240 V
- Wattage: 1.5, 3.5, 5 W
- Wattage equivalent: 5-20-50 W
- Energy efficiency label (EEL): A+

Product dimensions and weight

- Length: 5.4 cm

Rated values

- Rated beam angle: 36 degree(s)
- Rated lifetime: 15,000 h
- Rated luminous flux: 345 lm
- Rated peak intensity: 600 cd
- Rated power: 1.5-3.5-5 W

Technical specifications

- Frequency: 50-60 Hz



Issue date: 2023-11-08
Version: 0.615

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com