

PHILIPS

Linear tube

LED

19.5 W-54 W

G13

Cool White

Non-dimmable



8718696710975



Durable LED task lighting with excellent light quality

Upgrading to Philips LED tubes is a fast and easy way to replace your old fluorescent tubes with modern and efficient LED technology. This Philips LED tube is perfect for places that require a lot of light.

Choose for a sustainable solution

- Long-life tubes – Lasts up to 15 years
- Saves up to 80% energy

Light beyond illumination

- Instant on

Highlights

15,000-hour rated average life



With a lifetime of up to 15,000 hours, you can reduce the hassle of

frequently replacing your light tubes and enjoy a perfect lighting solution for over 15 years.

Instant on

Saves up to 80% energy



Enjoy the energy savings of LEDs without sacrificing light quality. Instantly save over 80% in energy by replacing your existing incandescent or halogen bulbs

Specifications

Bulb characteristics

- Dimmable: No
- Intended use: Indoor
- Lamp shape: Tube, double-ended
- Socket: G13
- Technology: LED
- Type of glass: Frosted

Lamp dimensions

- Height: 151.3 cm
- Weight: 0.27 kg
- Width: 2.8 cm

Durability

- Average life (at 2.7 hrs/day): 15 a
- Lumen maintenance factor: 70%
- Nominal lifetime: 15,000 h
- Number of switch cycles: 50,000

Light characteristics

- Application: Public spaces, Road and residential
- Beam angle: 240 degree(s)
- Colour consistency: 6SDCM
- Colour rendering index (CRI): 80
- Colour temperature: 4000 K
- Light Colour Category: Cool White
- Nominal luminous flux: 2000 lm
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light
- Colour Code: 840 | CCT of 4000K

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Lamp current: 155 mA
- Efficacy: 102 lm/W

Packaging dimensions and weight

- Net weight: 0.270 kg

Packaging information

- EAN: 8718696710975
- EOC: 871869671097501
- Product title: LED T8 1500mm 20W
G13 CW ND 1CT/4 UK

Power consumption

- Power factor: 0.5
- Voltage: 220–240 V
- Wattage: 19.5 W
- Wattage equivalent: 54 W
- Energy efficiency label (EEL): F

Product dimensions and weight

- Length: 151.3 cm

Rated values

- Rated beam angle: 240 degree(s)
- Rated lifetime: 15,000 h
- Rated luminous flux: 2000 lm
- Rated power: 19.5 W

Technical specifications

- Frequency: 50–60 Hz
- EPREL registration number: 491,860



Issue date: 2023-11-08
Version: 0.987

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com