

# PHILIPS

## Dimmer switch

Hue

Wireless installation

Battery powered

Easy access to light recipes

Use as a remote control



8718696743157



## Control your lights

Control and dim your lights with a Hue dimmer switch. Both a wall switch and remote control, this smart switch attaches easily to walls with the included adhesive and can be removed from the magnetic base to use as a remote control.

### Limitless possibilities

- Switch between light scenes
- Brighten and dim your smart lights
- Mount the dimmer switch anywhere
- Connect up to 10 smart lights
- Use as a remote control dimmer

# Highlights

## Switch between light scenes



The smart Dimmer Switch allows you to toggle through four light recipes by simply pressing the "on" switch. Energise, Concentrate, Read, and Relax are programmed by default and you can customise your selection in the Hue app.

## Mount anywhere



The Philips Hue Dimmer switch functions as a normal wall switch and dimmer – but better. In addition to mounting with screws or strong adhesive tape, you can remove the magnetic control and carry it with you anywhere.

## Use as a remote control dimmer



The Hue Dimmer switch is magnetic and can be removed from the base plate, allowing you to use the dimmer switch as a handy remote control.

## Brighten and dim your lights



The Philips Hue Dimmer switch allows you to wirelessly turn your lights up high or down low.

## Connect up to 10 smart lights



With the Philips Hue wireless dimming kit for smart lights, you can connect up to 10 lights to control simultaneously from a single dimmer switch.

# Specifications

## Environmental

- Operational humidity: 5% <H<95% (non-condensing)
- Operational temperature: -10°C – 45°C

## Extra feature/accessory incl.

- Portable: Yes

## Guarantee

- 2 years: Yes

## Service

- Warranty: 2 year(s)

## Technical specifications

- Number of configurable buttons: 2
- Weight: 37
- Battery type: CR – Button cell

**The switch**

- Batteries included: 1 x CR2450
- Configurable buttons: 2
- Frequency band: 2400 - 2483.5 MHz
- IP rating: IP20
- Lifetime: 50000 clicks
- Max. lights per switch: 10 if not linked to Hue bridge
- Minimal battery lifetime: 3 a
- Mounting options: wall, freestanding
- Software upgradeable: when connected to Hue Bridge
- Switch depth: 11 mm
- Switch height: 92 mm
- Switch width: 35 mm
- Wall plate depth: 14 mm
- Wall plate height: 115 mm
- Wall plate width: 70 mm
- Weight including wall plate: 67 g
- Weight of switch: 37 g
- Zigbee Light link: IEEE 802.15.4 Protocol

- Minimal range indoor: 500 in

**What's in the box**

- Hue dimmer switch: 1

**What's supported**

- Philips Hue App: IOS 11 and later, Android 7.0 and later
- Voice assistants: Amazon Alexa, Google Assistant, Apple HomeKit (Via Hue Bridge), Microsoft Cortana (Via Hue Bridge)

**Packaging dimensions and weight**

- EAN/UPC - product: 8718696743157
- Net weight: 0.100 kg
- Gross weight: 0.154 kg
- Height: 16.500 cm
- Length: 5.500 cm
- Width: 8.800 cm
- Material number (12NC): 929001173761



Issue date: 2023-11-08  
Version: 0.632

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)