

PHILIPS

Wireless dimming kit
E27

Hue White

Soft white light

Instant control via Bluetooth

Control with app or voice*

Dimmer switch included

8718696785331



Easy smart lighting

Get started with the Philips Hue wireless dimming kit and enjoy smooth wireless dimming. It works straight out of the box. Control the bulb with the included dimmer switch or connect to the Hue bridge to unlock more smart features.

Limitless possibilities

- Brighten and dim your smart lights
- Expand to a smart light system with the Hue Bridge
- Mount the dimmer switch anywhere
- Connect up to 10 smart lights


Highlights

Brighten and dim your lights



The Philips Hue Dimmer switch allows you to wirelessly turn your lights up high or down low.

Expand with Hue Bridge



When connected to a Hue Bridge (*sold separately), your smart lights become even more versatile. Control your lights from anywhere inside and outside your home using just the Philips Hue app. Set timers, routines and add or remove lights from your system.

Mount anywhere



The Philips Hue Dimmer switch functions as a normal wall switch and dimmer – but better. In addition to mounting with screws or strong adhesive tape, you can remove the magnetic control and carry it with you anywhere.

Connect up to 10 smart lights



With the Philips Hue wireless dimming kit for smart lights, you can connect up to 10 lights to control simultaneously from a single dimmer switch.

Specifications

Lamp dimensions

- Dimensions (WxHxD): 61x110

Environmental

- Operational humidity: 5% <H<95% (non-condensing)
- Operational temperature: -10 °C – 45 °C

Extra feature/accessory incl.

- Dimmable with the Hue app and switches: Yes

Guarantee

- 2 years: Yes

Service

- Warranty: 2 year(s)

Technical specifications

- Weight: 67
- Bulb technology: LED

The bulb

- Colour temperature: 2700K
- Diameter: 61 mm
- Energy efficiency label: A+
- Fitting: E27
- Form factor: A60
- Height: 110 mm
- Input voltage: 220V–240V
- Lifetime: 25,000 h
- Light output: Warm white light
- Lumen output: 806 lm
- Max. operation power: 9 W
- Max. standby power: 0.5 W
- Number of switching cycles: 50,000
- Power factor: 0.5
- Rated lifetime: 25,000 h
- Software upgradable: Yes
- Start up: Instant 100% light output
- Wattage: 9 W
- Wattage equivalent: 60 W
- Communication protocol: Bluetooth and Zigbee
- Software upgradable: When connected to Bluetooth app or Hue Bridge

The switch

- Batteries included: 1 x CR2450
- Frequency band: 2400 – 2483.5 MHz
- IP rating: 20
- Lifetime: 50000 clicks
- Max. lights per switch: 10 if not linked to Hue bridge
- Minimal battery lifetime: 3 a
- Mounting options: freestanding
- Special features: Not applicable
- Switch depth: 11 mm
- Switch height: 92 mm
- Switch width: 35 mm
- Wall plate depth: 14 mm
- Wall plate height: 115 mm
- Wall plate width: 70 mm
- Weight including wall plate: 67 g
- Weight of switch: 37 g
- Zigbee Light link: IEEE 802.15.4 Protocol

What's in the box

- Hue bulbs: 1
- Hue dimmer switch: 1

What's supported

- HomeKit compatible: Yes
- IOS: 7 or later
- Philips Hue App: IOS 13 and above, Android 8.0 and above
- Voice assistants: Amazon Alexa
- Philips Hue Bluetooth App: IOS 11 and later, Android 7.0 and later

Packaging dimensions and weight

- EAN/UPC – product: 8718696785331
- Net weight: 0.180 kg
- Gross weight: 0.292 kg
- Height: 16.500 cm
- Length: 7.500 cm
- Width: 17.600 cm
- Material number (12NC): 929001821603



Issue date: 2023-11-08
Version: 0.537

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com