



PHILIPS  
LED  
Bulb (Dimmable)  
6.5W-25W  
E27  
Flame  
Dimmable



8718699629502

## Complete the vintage look

This Philips Vintage cord combines a fabric wire and metal socket with matt finishing to bring a retro vibe to your living space. Paired with a E27 LED bulb from the Philips Vintage range to complete the vintage look.

### High quality light

- Designed for the comfort of your eyes

### Designed for your living- and bedroom

- High quality material
- Adjustable cord length

### Choose a simple replacement for your old bulbs

- Vintage range

# PHILIPS

# Highlights

## Gentle LEDs, easy on the eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get the glare. Too soft and you experience

flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

## High quality material [Chord]

This beautiful fabric covered cord ensures your lamp hangs straight when installed. The matt satin finishing of the metal socket enhances the antique look of any bulb.

## Adjustable cord length [Cord]

Cord is fully adjustable for various heights giving the flexibility to arrange a stylish dynamic combination of suspension lighting above your kitchen island and dining table.

## Vintage range

The Philips Vintage collection is available in an array of giant shapes, candles and other familiar form factors, to provide a seamless fit across your space.

# Specifications

## Bulb characteristics

- Dimmable: Yes
- Intended use: Indoor
- Lamp shape: Accessory
- Socket: E27
- Technology: LED

## Bulb dimensions

- Height: 28.6 cm
- Weight: 0.31 kg
- Width: 20 cm

## Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 0.7
- Nominal lifetime: 15,000 h

## Light characteristics

- Color consistency: 6 SDCM
- Color rendering index (CRI): 80
- Color temperature: 2000 K
- Light Color Category: Flame
- Nominal luminous flux: 470 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light

## Miscellaneous

- EyeComfort: Yes

## Other characteristics

- Lamp current: 40 mA
- Mercury content: 0 mg
- Efficacy: 72 lm/W

## Packaging information

- Family: LED

## Power consumption

- Power consumption per 1000h: 7 kW
- Power factor: 0.7
- Voltage: 230 V
- Wattage: 6.5 W
- Wattage equivalent: 40 W
- Energy Efficiency Label: A+

## Rated values

- Rated lifetime: 15,000 h
- Rated luminous flux: 470 lumen
- Rated power: 6.5 W

**Packaging dimensions & weight**

- EAN/UPC - product: 8718699629502
- Net weight: 0.660 kg
- Gross weight: 1.200 kg
- Height: 38.500 cm
- Length: 22.500 cm
- Width: 22.500 cm
- EAN/UPC - Piece: 8718699629502
- Material number (12NC): 929001873499
- EAN/UPC - Case: 8718699629519
- Weight product including package: 1.200 kg
- Weight product without package: 0.660 kg
- SAP Height (Piece): 38.500 cm
- SAP Length (Piece): 22.500 cm
- SAP Width (Piece): 22.500 cm



Issue date: 2020-02-24  
Version: 0.508

© 2020 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)