

LuxSpace Surface Mounted

Installation instructions

Instructions de montage
Montageanleitung
Montage instructie

Instrucciones de montaje
Instruções de montagem
Monteringsinstruktioner
Monteringsvejledning

Kokoonpano- ja kiinnitysohjeet
Montaj yönergeleri
Instrukcja montażu
Οδηγί ες συναρμολογησης

Szerelési utasítások
Návod k montáži
Návod k montáži
ИНСТРУКЦИЯ ПО МОНТАЖУ

indoor



EN
60598

IP20

50/60Hz



850°C



ØA



H

T° K


P max





DN560C DN561C	LED8S	250 mm	142 mm	830	9 W	1,40 kg
				840		
				827		
				830		
	LED12S			840	13 W	
				930		
				827		
				830		
	LED12S			840	13 W	
				930		
				827		
				830		
DN570C DN571C	LED20S	300 mm	178,5 mm	840	21 W	1,99 kg
				930		
				827		
				830		
	LED24S			840	26 W	
				930		
				827		
				830		




STATIC





DALI




- PG or PGO Front Face Covers
- Suspended Glass Deco Accessories







1a




1b



1c




STATIC



2b




DALI for Main Supply




2a


2c




DN570C / DN571C




3a




3c



3b




3d





DN570C-DN571C LED24S 4000K : Groupe de risque 1 suivant la norme IEC 62471:2006 / Risk group 1 according to IEC 62471:2006


DN560C / DN561C



4a




ZBS260 OCS.



Chiffon doux
Soft cloth
Weiches Tuch
Zacht doekje
Panno morbido
Tejido Suave
Blødt stykke stof
Pehmeä kangas
Mięka ściereczka
Pano macio

4b



Dali dimming
range 1/100%

	XITANIUM 17W LH 0.3-1A 24V I 230V	XITANIUM 17W LH 0.3-1A 24V TD/Is 230V	XITANIUM 20W LH 0.15-0.5A 48V Is 230V	XITANIUM 20W LH 0.15-0.5A 48V TD/Is 230V	XITANIUM 25W 0.3-1A 36V I 230V	XITANIUM 25W 0.3-1A 36V TD/Is 230V	LED Driver 25W 0.3-1A 36V I 230V
	Electrical Characteristics		Electrical Characteristics		Electrical Characteristics		
	✓	✓	✓	✓	✓	✓	✓
Inom (A)	0.15	0.11	0.12	0.11	0.2	0.2	0.15
Imax (A)	8	20	18	16	8	20	5.2
Tref (µs)	180	150	240	220	180	150	50
MCB	Nr. Drivers Max		Nr. Drivers Max		Nr. Drivers Max		
B-10A	x15	x18	x20	x15	x15	x18	x31
B-16A	x24	x30	x32	x24	x24	x30	x74
C-10A	x24	x31	x33	x24	x24	x31	x74
C-16A	x40	x51	x54	x40	x40	x51	x85

CLO Version



Pmax
@ t=0h Pmax
@ t=50000h

	LED8S	830	7,2 W	9 W
DN560B DN561B		840		
	LED12S	827	10,4 W	13 W
		830		
		840		
		930		
DN570B DN571B	LED12S	827	10,4 W	13 W
		830		
		840		
		930		



Pmax
@ t=0h Pmax
@ t=50000h

	LED20S	827	16,8 W	21 W
DN570B DN571B		830		
		840		
		930		
	LED24S	827	20,8 W	26 W
		830		
		840		
		930		



- DO NOT REPROGRAM THE DRIVER
- Constant light Output Option
stopped @ 50 000h.

CLO Table

Step	time (h)	P %
	0	80%
1	3000	81%
2	7000	83%
3	10000	84%
4	13000	85%
5	17000	87%
6	20000	88%
7	23000	89%
8	27000	91%
9	30000	92%
10	33000	93%
11	37000	95%
12	40000	96%
13	43000	97%
14	47000	99%
15	50000	100%

- F - L'installation peut exiger le conseil d'une personne qualifiée
UK - Installation may require advice from a qualified person
D - Installation kann Rat von einer qualifizierten Person erfordern
NL - De installatie kan raad van een gekwalificeerde persoon vereisen
I - L'installazione può richiedere il consiglio da una persona qualificata
SP - La instalación puede requerir consejo de una persona calificada
SW - Installationen kan behöva råd från en kvalificerad person
FL - Asennus saattaa edellyttää pätevän henkilön neuvoa
PL - Instalacja może wymagać porady wykwalifikowanej osoby
P - A instalação pode exigir o conselho de uma pessoa qualificada