

PHILIPS
Stonco

Wall Mount

Wall pack



Proven design meets LED technology

With efficacies up to 118 LPW, Philips Stonco's new LED Wall packs help you to upgrade from costly HID fixtures with confidence.

The Wall pack family features energy-saving LED technology, two different sizes & wattage choices of 30, 50 and 75W. The 50 watt Wall Pack provides the same illumination as a 100W HID, and uses over 50% less energy. The glass refractor lens design cuts down on glare, and the housing is one-piece die-cast aluminum for strength and durability.

Move into the future with time-proven design from a name you can trust.



Wall pack LED


WP30/WP50/WP75




- An easy switch from costly HID fixtures.
- Flexible options – choose from 30, 50 and 75 watts in two different sizes.
- The 50 watt Wall pack provides the equivalent illumination to 100W HID, and uses over 50% less energy.*
- Glass refractor lens design cuts down on glare.
- One-piece die-cast aluminum housing.
- 5 year limited warranty.

*Based on comparison between 100W HPS Wall pack at 115W providing 6100 lumens and 50W WP LED providing 5500 lumens

WP30



WP50 & WP75



Ordering guide

example: WP-50-NW-G1-8-BZ

Luminaire	Wattage	Generation	Voltage	Finish
WP		NW-G1	8	BZ
WP Wall Pack	30 30W 50 50W 75 75W	NW-G1 Neutral White, 4000K, 70CRI, Generation 1	8 120-277 Volts	BZ Bronze

© 2017 Philips Lighting Holding B.V. All rights reserved.
 Philips reserves the right to make changes in specifications and/or to discontinue any product at any time without notice or obligation and will not be liable for any consequences resulting from the use of this publication.
philips.com/luminaires



Philips Lighting North America Corporation
 200 Franklin Square Drive, Somerset, NJ 08873
 Tel. 855-486-2216

Philips Lighting Canada Ltd.
 281 Hillmount Rd, Markham, ON, Canada L6C 2S3
 Tel. 800-668-9008