

Philips Mini Koffer BGP 060

Mounting instructions

Instructions de montage

Montageanleitung

Montage instructie

Istruzioni di montaggio

Instrucciones de montaje

Instruções de montagem

Monteringsinstruktioner

Monteringsvejledning

Kokoonpano- ja kiinnitysohjeet

Montaj yönergesi

Οδηγίες συναρμολόγησης

Instrukcja montażu

Szerelési utasítások

Návod k montáži

Монтажная инструкция




220V
240V



IP66

IEC
EN60598

R&TTE
868MHZ<5mW



LINE

lumen

W
+/-10%

LED



EL














IK







LED	GRN16-2S/830	1600	20	16	●	●	●	●	07	6.2
LED	GRN20-2S/740	1960	20	16	●	●	●	●	07	6.2
LED	GRN21-2S/657	2080	20	16	●	●	●	●	07	6.2
LED	GRN24-2S/830	2400	29	24	●	●	●	●	07	6.2
LED	GRN29-2S/740	2930	29	24	●	●	●	●	07	6.2
LED	GRN31-2S/657	3120	29	24	●	●	●	●	07	6.2
LED	ECO23-2S/830	2320	29	16	●	●	●	●	07	6.2
LED	ECO28-2S/740	2840	29	16	●	●	●	●	07	6.2
LED	ECO30-2S/657	3020	29	16	●	●	●	●	07	6.2
LED	ECO35-2S/830	3480	41	24	●	●	●	●	07	6.2
LED	ECO43-2S/740	4250	41	24	●	●	●	●	07	6.2
LED	ECO45-2S/657	4530	41	24	●	●	●	●	07	6.2


Mini Koffer LED BGP 060







LUMISTEP



D7 I-10V



Number of LED	GreenLine Ecoline
16	OK only for 7-10V
24	●


D9 DALI




Number of LED	GreenLine Ecoline	GreenLine Ecoline
16	OK only for 178-255	OK only for 241-255
24	●	●

DYNADIMMER


DD1/DDF1
Road 40% saving



DD2/DDF2
Road 32% saving



DD3/DDF3
Road 50% saving



RF

