


# PHILIPS ADVANCE

## Electrical Specifications

VH-1Q26-TP-W	
Brand Name	COMPACT-HPF
Ballast Type	Magnetic
Starting Method	Pre-Heat
Lamp Connection	Series
Input Voltage	277
Input Frequency	60 HZ
Status	Active

Lamp Type	Num. of Lamps	Rated Lamp Watts	Min. Start Temp (°F/°C)	Input Current (Amps)	Starting Current (Amps)	Open Circuit (Amps)	Input Power (Watts)	Ballast Factor	MAX THD %	Power Factor
* CFM26W/GX24D	1	26	50/10	0.11	0.38	0.24	32	0.96	20	1.00
CFQ26W/G24D	1	26	50/10	0.11	0.38	0.24	31	0.90	20	1.00

## Wiring Diagram



### Diag. 47


The wiring diagram that appears above is for the lamp type denoted by the asterisk (\*)

### Standard Lead Length (inches)

	in.	cm.
Black		0
White	15	38.1
Blue	15	38.1
Red		0
Yellow		0
Gray		0
Violet		0

	in.	cm.
Yellow/Blue		0
Blue/White		0
Brown		0
Orange		0
Orange/Black		0
Black/White	15	38.1
Red/White		0

## Enclosure



### Enclosure Dimensions

OverAll (L)	Width (std)/(TP)	Height (H)	Mounting (M)
4.75 "	2.21875 "/0 "	1.625 "	4.375 "
4 3/4	2 7/32 / 0	1 5/8	4 3/8
12.1 cm	5.6 cm / 0 cm	4.1 cm	11.1 cm



Revised 07/01/99

Data is based upon tests performed by Philips Lighting N.A in a controlled environment and representative of relative performance. Actual performance can vary depending on operating conditions. Specifications are subject to change without notice. All specifications are nominal unless otherwise noted.

## Philips Lighting Electronic N.A

10275 West Higgins Road Rosemont, IL 60018 Tel.: 800-322-2086 Fax: 888-432-1882  
Customer Support/Technical Service: 800-372-3331 · OEM Support: 866-915-5886