



Typical complete installation shown (Power Head, Reflector and Aperture Disk must be ordered separately).

Ordering Information

Catalog No.	Description	Power Cord	Power Cord Color	Adapter Finish	Overall Height Max.
409DGLS	9", Pendalyte Deco track mounting kit	SJT 18-3	Gray	Silver	120"
409DBLS	9", Pendalyte Deco track mounting kit	SJT 18-3	Black	Titanium	120"
412DLS*	12", Pendalyte Deco track mounting kit	SJT 18-3	Gray	Silver	120"
416DLS	16", Pendalyte Deco track mounting kit	SJT 18-3	Gray	Silver	120"

*Not compatible with 12" performance, 26/32/42W two-light dimming or 50/70W dimming.

Features

- 1. **Power Adapter:** Titanium or silver molded polycarbonate.
- 2. **Power Cord:** 3 wire, SJT 18-3, Black or Gray.
- 3. **Support Adapter:** Supports pendant weight. Silver or Titanium.
- 4. **Support Cable:** 1/16" stainless steel.
- 5. **Support Arms:** (3) 3/8" diameter steel tubing, brushed and clear lacquered.

Ordered Separately From Deco Track Mounting Kit

- 6. **Power Head:** Order separately, see standard Pendalyte specification sheets for more details.
- 7. **Reflector, Refractor, Glass Shade:** Order separately. See standard Pendalyte specification sheets for more details.
- 8. **Aperture Disk:** Order separately. See standard Pendalyte specification sheets for more details. See specification sheet 404BLS for track mounting kit for use with non-Deco units.
- 9. **Track:** Compatibility with Basic®, Advent®, and Radius® Lytespan Track

Labels

cULus.

Job Information	Type:
Job Name:	
Cat. No.:	
Lamp(s):	
Notes:	