

**PHILIPS**  
**LIGHTOLIER**



Track

Alcyon LED

Horizontal Cylinder,  
LLAH, 15W/1100lm



---

# An impactful option for retail display areas

**Alcyon LED Horizontal Cylinder** is a single optic platform designed to deliver superior optical performance.

Alcyon LED Horizontal Cylinder is ideal for display, accent and task lighting. These cylinders provide higher efficiency than incandescent or halogen light sources leading to energy savings with no ultraviolet or infrared radiation. Luminaires provide concentrated light which dramatically draws interest to objects and elements in a space.

For further details and availability, please contact your authorized Philips representative.



## Alcyon LED Horizontal Cylinder

Excellent beam control and aesthetics while providing high performance for accent lighting needs in retail and commercial applications.

### CrispWhite Technology

The CrispWhite technology combines the warm, saturated colors of high CRI with crisp and vibrant whites. The small form factor and high quality of light make this an impactful option for retail display areas.

[www.philipslumileds.com/products/luxeon-cob-with-crispwhite](http://www.philipslumileds.com/products/luxeon-cob-with-crispwhite)

### Features

- Efficacy: 76+ lm/W
- Lumens: 1100lm
- Wattage: 14.8W
- CCT: 2700K up to 4000K
- CRI: 80 & 90 (min)
- CrispWhite: 90CRI/3000K
- Field changeable optics
- Rated Life: 50,000hrs (min.) at 70% lumen maintenance
- Warranty: Standard 5 year limited warranty

#### Optical assembly:

Interchangeable reflectors may be changed at any time to accommodate the lighting requirements of the space.

#### Integral locking:

Vertical and horizontal locking preserves original lighting design intent.

#### Aiming indicator:

Allows a series of luminaires to be precisely set to the same aiming angle.

### Ordering guide



example: LLAH11930BKTECW

Series	Lumens	CRI/CCT*	Finish	Dimming	Options
<b>LLAH</b>	<b>11</b>				
<b>LLAH</b> Alcyon LED Horizontal Track Cylinder	<b>11</b> 1100lm	<b>830</b> 80 CRI/3000K <b>835</b> 80 CRI/3500K <b>840</b> 80 CRI/4000K <b>927</b> 90 CRI/2700K <b>930</b> 90 CRI/3000K	<b>AL</b> Aluminum <b>BK</b> Black <b>WH</b> White	<b>TE</b> Triac/ELV	— None (leave blank) <b>CW</b> CrispWhite

\* CrispWhite can only be ordered with 90/30 CRI/CCT combination. For other configurations and variations please contact the factory.

example: LLRS

Series	Reflector
<b>LL</b>	
<b>LL</b> Alcyon LED Horizontal Track Cylinder	<b>RS</b> 13° Spot <b>RNF</b> 22° Narrow Flood <b>RF</b> 28° Flood



Visit [philips.com/warranties](http://philips.com/warranties) for more information on the standard 5-year limited warranty.



© 2015 Koninklijke Philips N.V. All rights reserved. Philips reserves the right to make changes in specifications and/or to discontinue any product at any time without notice or obligation and will not be liable for any consequences resulting from the use of this publication.



Philips Lighting, North America Corporation  
200 Franklin Square Drive, Somerset, NJ 08873  
Tel. 855-486-2216

Imported by: Philips Lighting,  
A division of Philips Electronics Ltd.  
281 Hillmount Rd, Markham, ON, Canada L6C 2S3  
Tel. 800-668-9008