

# LIGHTOLIER

by  signify

Track Lighting

Alcyon LED

LLAH Horizontal Cylinder



## An impactful option for retail display areas

A single optic platform designed to deliver superior optical performance that is ideal for display, accent and task lighting.

### Benefits

Cylinders provide higher efficiency than incandescent or halogen light sources leading to energy savings with no ultraviolet or infrared radiation. Luminaires provide concentrated light which dramatically draws interest to objects and elements in a space.

For further details and availability, please contact your authorized representative.

### CrispWhite Technology

The CrispWhite technology combines the warm, saturated colors of high CRI with crisp and vibrant whites. The small form factor and high quality of light make this an impactful option for retail display areas.

[www.lumileds.com/products/luxeon-cob-with-crispwhite](http://www.lumileds.com/products/luxeon-cob-with-crispwhite)



# LLAH Alcyon LED

## Horizontal Cylinder track lighting

### Features

**Efficacy:** 76+ lm/w  
**Lumens:** 1100  
**Watts:** 15W  
**CRI:** 80 & 90 (min)  
**CCT:** 2700K, 3000K, 4000K  
**Volts:** 120V (50/60Hz)  
**Dimming:** Triac and ELV (trailing edge)  
**Lifetime:** 50,000 hrs (L70)  
**Labels:** ENERGY STAR®  
**Warranty:** 5 year



**Integral locking with aiming indicator**  
 Vertical and horizontal locking preserves original lighting design intent and allows a series of luminaires to be precisely set to the same aiming angle.



**Optical assembly**  
 Featuring Spot (RS), Narrow Flood (RNF) and Flood (RF) field changeable reflectors that can be changed at any time to accommodate lighting requirements.

**Fixture** Complete luminaire = Fixture + Reflector + Accessories (optional) example: LLAH11930BKTECW

Series	Lumen	CRI/CCT	Finish	Options
LLAH Alcyon LED Horizontal Cylinder	11 1100lm	830 80 CRI/3000K 835 80 CRI/3500K 840 80 CRI/4000K 927 90 CRI/2700K 930 90 CRI/3000K <sup>1</sup>	WH Matte White BK Matte Black AL Aluminum	TE Triac/ELV TECW Triac/ELV with CrispWhite


1. CrispWhite can only be ordered with 90/30 CRI/CCT (930) combination.

### Reflector

Series	Beams
LL Accessory	RS 13° Spot RNF 22° Narrow Flood RF 28° Flood

**Note:** Contact factory for other configurations.

### Dimensions



### Mounting

For use with Radius, Basic and Advent track. For monopoint applications refer to specification sheet 6173.

Not compatible with extension wands, or sloped ceiling adapter.

### Dimming

**ELV and Triac dimming compatible**  
 Signify Sunrise SR400RPC120 (100-5%)  
 Signify Sunrise ZP425QE (100-4%)  
 Lutron Skylark SELV-300P (100-5%)  
 Lutron MAELV-600 (100-2%)  
 Leviton Decora IPE04 (100-3%)  
 Leviton Decora 6615-POW (100-8%)

### Accessories

Series	Style
LLA01AH Accessory Holder	WH Matte White BK Matte Black
LLA01SN Snoot	WH Matte White BK Matte Black
AL25HC Hex Cell Louver	— Matte Black

**AF25/ADF25**  
 Diffusion/Color filters (contact factory)

**Note:** When using two accessories must use holder.



Visit [Signify.com/warranties](https://www.signify.com/warranties) for more information on Signify's standard 5-year limited warranty.

See specification sheet LLAH for additional drawings and technical information.

