



PHILIPS  
TL-D Super 80  
Linear fluorescent tube  
18 W  
G13  
Cool white

927980284036

# Vibrant experience with extra brightness

Philips Color 80s offer higher light output for extra brightness and better ambiance. They are suitable for applications where light quality is important for a more vibrant experience.

#### **Saves energy**

- Saves energy

#### **Gives you bright light**

- Vibrant experience with extra brightness

# PHILIPS

# Highlights

## Saves energy Bright boost

High efficient fluorescent combined with BrightBoost technology for good color rendering and extra brightness

# Specifications

## Bulb characteristics

- Dimmable: No
- Socket: GU10

## Durability

- Nominal lifetime: 15,000 hour(s)

## Light characteristics

- Color rendering index (CRI): 82
- Light Color Category: Cool White

## Power consumption

- Wattage: 18 W

## Technical specifications

- Light output: 1,350 lumen
- Shape: Linear fluorescent tube

## Packaging dimensions & weight

- SAP EAN/UPC - Piece: 8711500285607
- EAN/UPC - Case: 8711500285812
- SAP Gross Weight EAN (Piece): 0.093 kg
- Net Weight (Piece): 0.070 kg
- SAP Height (Piece): 2.700 cm
- SAP Length (Piece): 60.600 cm
- SAP Width (Piece): 2.700 cm



Issue date: 2019-09-08  
Version: 0.319

© 2019 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)