



PHILIPS
TL-D Super 80
Linear fluorescent tube
36 W
G13
Warm white

927982283036

Vibrant experience with extra brightness

Philips Color 80s offer higher light output for extra brightness and better ambiance. They are suitable for applications where light quality is important for a more vibrant experience.

Saves energy

- Saves energy

Gives you bright light

- Vibrant experience with extra brightness

PHILIPS

Highlights

Saves energy Bright boost

High efficient fluorescent combined with BrightBoost technology for good color rendering and extra brightness

Specifications

Bulb characteristics

- Dimmable: No
- Socket: GU10

Durability

- Nominal lifetime: 15,000 hour(s)

Light characteristics

- Color rendering index (CRI): 83
- Light Color Category: Warm White

Power consumption

- Wattage: 36 W

Technical specifications

- Light output: 3,250 lumen
- Shape: Linear fluorescent tube

Packaging dimensions & weight

- SAP EAN/UPC - Piece: 8711500285591
- EAN/UPC - Case: 8711500285874
- SAP Gross Weight EAN (Piece): 0.165 kg
- Net Weight: 0.140 kg
- SAP Height (Piece): 2.700 cm
- SAP Length (Piece): 121.500 cm
- SAP Width (Piece): 2.700 cm



Issue date: 2019-12-16
Version: 0.379

© 2019 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com