



PHILIPS
TL-E Super 80
Circular fluorescent
32 W
G10q
Cool daylight

928026386574

Vibrant experience with extra brightness

Philips Color 80s offer higher light output for extra brightness and better ambiance. They are suitable for applications where light quality is important for a more vibrant experience.

Saves energy

- Saves energy

Gives you bright light

- Vibrant experience with extra brightness

PHILIPS

Highlights

Saves energy Bright boost

High efficient fluorescent combined with BrightBoost technology for good color rendering and extra brightness

Specifications

Bulb characteristics

- Dimmable: No
- Socket: G10Q

Durability

- Nominal lifetime: 8,000 hour(s)

Light characteristics

- Color rendering index (CRI): 85
- Light Color Category: Cool Daylight

Power consumption

- Wattage: 32 W

Technical specifications

- Light output: 2,310 lumen
- Shape: Circular fluorescent

Packaging dimensions and weight

- EAN/UPC - product: 8711500640383
- Net weight: 0.110 kg
- Gross weight: 0.300 kg
- Height: 30.500 cm
- Length: 3.500 cm
- Width: 30.800 cm
- SAP EAN/UPC - Piece: 8711500640383
- Material number (12NC): 928026386574
- EAN/UPC - Case: 8727900813616
- SAP Gross Weight EAN (Piece): 0.300 kg
- Net Weight: 0.110 kg
- SAP Height (Piece): 30.500 cm
- SAP Length (Piece): 3.500 cm
- SAP Width (Piece): 30.800 cm



Issue date: 2020-02-20
Version: 0.422

© 2020 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com