



PHILIPS  
TL-D Standard colours  
Linear fluorescent tube  
58 W  
G13  
Cool daylight

928049005482

# Reliable, functional lighting

Philips Color 80s offer higher light output for extra brightness and better ambiance. They are suitable for applications where light quality is important for a more vibrant experience.

## **Gives you bright light**

- Standard colors with moderate color rendering
- High initial light output

# PHILIPS

# Highlights

## Standard colors High initial light output

High Light output provides better light quality with more brightness and

allows more vibrance in home application.

# Specifications

## Bulb characteristics

- Dimmable: No
- Socket: GU10

## Durability

- Nominal lifetime: 13,000 hour(s)

## Light characteristics

- Color rendering index (CRI): 75
- Light Color Category: Cool Daylight

## Power consumption

- Wattage: 58 W

## Technical specifications

- Light output: 3,925 lumen
- Shape: Linear fluorescent tube

## Packaging dimensions and weight

- EAN/UPC - product: 8711500702753
- Net weight: 0.230 kg
- Gross weight: 0.260 kg
- Height: 2.700 cm
- Length: 150.000 cm
- Width: 2.700 cm
- SAP EAN/UPC - Piece: 8711500702753
- Material number (12NC): 928049005482
- EAN/UPC - Case: 8711500728234
- SAP Gross Weight EAN (Piece): 0.260 kg
- Net Weight: 0.230 kg
- SAP Height (Piece): 2.700 cm
- SAP Length (Piece): 150.000 cm
- SAP Width (Piece): 2.700 cm



Issue date: 2020-03-16  
Version: 0.422

© 2020 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)