


Linear

TruGroove Suspended

4800 lm/4ft, Indirect
3000/3500/4000K



Project: _____

Spec Type: _____

Catalog No: 2903LxCNQ _____

Qty _____

Line Notes: _____

TruGroove Recessed is driving performance beyond the edge. Innovative optics deliver exceptional uniformity and wide row spacing from a 3" aperture continuous line-of light. An extended family and refined design are perfect for lighting any professional space.

Ordering guide

Product Type	Source	Color Temp *	Lumens *	Lower Optics	Upper Optics	Run Length	Wiring †	Voltage	Driver	Finish
2903	L		C	N	Q					
TruGroove Suspended Indirect	L LED	A 4000K B 3500K C 3000K	C 4800 lm/4ft E 3200 lm/4ft	N None	W Asymmetric Performance Q Symmetric Performance	04 4' 06 6' 08 8' A4 2'x2' Total run length (2' increments)	7 1 cct Dimming M 1 cct Dimming + EM Wiring N 1 cct Dimming + EM Batt. Pack	1 120V 2 277V 3 347V	E Philips Advance 0-10V (1% dim)	W Standard White T Titanium Silver B Black C Custom

* Nominal values within a range. Consult photometry data for color temp, lumens & distribution of chosen configuration.


† Not all wiring types are available with all configurations. Consult Philips Ledalite for a complete list of available options.

Mounting Hardware

Mount Type
Consult separate mounting spec sheet for mount type options

Suspension Length
Distance from ceiling to top of luminaire in inches

Endcaps - Flat Grooved



TruGroove Suspended

4800 lm/4ft, Indirect

3000/3500/4000K

Optical System

Upper hemisphere: White light emitted from a linear array of upward-facing LEDs is shaped into a homogeneous, wide-throw batwing distribution using either a freeform elliptical lens or an engineered light guide panel.

Lower hemisphere: White light emitted from a linear array of downward-facing LEDs is laterally redirected using either a biconvex lens or optical microstructures embedded in a layer of MesoOptics DX film. An extruded acrylic lens and MesoOptics film assembly then generates an optimal batwing distribution and a uniform continuum of light.

Endcaps

Diecast flat aluminum endcaps with integral groove to match housing.

Finish

High quality powder coated, available in matte white, black or titanium silver. Other custom colors available on request. White sensors only.

Housing

Precision aluminum extrusion, post painted.

Weight

Maximum: Suspended & Surface 3.9lb/ft, Wall 4.1lb/ft & 2'x2' Corner unit 21lb

Electrical

Factory pre-wired to section ends with quick-wire connectors.

Standard Drivers

Philips Advance Xitanium 0-10V, 1-100%.

Philips Advance Xitanium SR, 5-100% (for SpaceWise DT).

Class 2 rated output. Consult Philips Ledalite for other available drivers.

Standard Battery Pack

Philips Bodine, 90 min, 10W, Class 2 rated output,

Emergency lumen output = 10W x luminaire efficacy x 1.1.

Typical output: 1100lm.

Lumen Maintenance

At an ambient temperature of 25°C, the LED lumen maintenance expectation according to IES TM-21-11 is:

L80 (12k) 60,000 hrs (**Reported** methodology)

L80 (6k) 110,000 hrs (**Projected** methodology).

Source Color

LEDs rated for color rendering CRI >80, R9 >0 and fixture to fixture color accuracy within 2 SDCM.

Controls

Suspended version available with the following integrated controls:

Response daylight sensor (for single zone).

SpaceWise DT occupancy & daylight sensor w/ advanced grouping & dwell time.

SpaceWise DT commissioning via Android phone and Philips Field App. Compatible dimming wireless wall switches are available. For more information, please refer to www.philips.com/spacewise

Mounting

Suspended: Variable sling mount allows +/- 5" of horizontal adjustment from joint or end. Aircraft cable and tamper-resistant gripper provide unlimited vertical adjustment and are independently tested to stringent safety standards.

Wall: A hidden steel rail and bracket system attaches to the existing structure and supports housings close to the wall. Mount positioning is fully variable along the modules to accommodate site conditions, spaced up to 4½' on center and within 12" of an end or joint.

Surface: Fixture is mounted flush to surface using hidden brackets that attach to existing structure, variable between 0.6"-1.7" from end or joint.

Joints

Self-aligning joining system with hands-free pre-joining wire access.

Approvals

Certified to UL, CSA and IES standards. Certain symmetric indirect/direct and indirect versions are DesignLights Consortium® qualified. Please see the DLC QPL list for exact catalog numbers (www.designlights.org/QPL).

Warranty


Philips indoor professional luminaires 5 year LED warranty: <http://www.philips.com/warranties>

Environment

Rated for dry or damp locations in operating ambient temperatures 0-40°C (32-104°F). Certain luminaire components may be adversely affected by contaminants. Damage caused by sulfur, chlorine, petroleum based solutions or other contaminants in the area of operation are not covered under warranty. Not suitable for natatorium environments.

Due to continuing product improvements, Philips Ledalite reserves the right to change the specifications without notice.

Dimensions - Cross Section




TruGroove Suspended


4800 lm/4ft, Indirect
3000/3500/4000K

Dimensions - Modules

Suspended Linear Modules Without Endcaps - Side View




Suspended 2'x2' Corners Without Endcaps - Top View



TruGroove Suspended

4800 lm/4ft, Indirect
3000/3500/4000K

Photometry - 3500K



Candela Distribution

Vertical Angle	Horizontal Angle					Zonal Lumens
	0	22.5	45	67.5	90	
0	0	0	0	0	0	0
5	0	0	0	0	0	0
15	0	0	0	0	0	0
25	0	0	0	0	0	0
35	0	0	0	0	0	0
45	0	0	0	0	0	0
55	0	0	0	0	0	0
65	0	0	0	0	0	0
75	0	0	0	0	0	0
85	0	0	0	0	0	0
90	0	0	0	0	0	0
95	21	32	32	35	36	41
105	86	111	407	1168	1423	585
115	247	347	860	1564	2001	964
125	596	671	968	1470	1729	953
135	715	775	991	1314	1473	808
145	801	842	986	1167	1262	632
155	850	869	947	1022	1057	440
165	869	877	907	930	941	257
175	877	875	880	880	880	84
180	877	877	877	877	877	0

Values per 4ft unit

Fixture photometry has been conducted in accordance with IESNA LM-79-08

IES files for this and other photometric options can be downloaded online at www.lightingproducts.philips.com

Coefficients of Utilization (%)

RCR	Ceiling Wall					80					70					50					0				
	70	50	30	10	70	50	30	10	70	50	30	10	70	50	30	10	70	50	30	10	70	50	30	10	70
0	95	95	95	95	81	81	81	56	56	56	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
1	87	83	79	76	74	71	68	48	47	45	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
2	79	72	66	62	67	62	57	42	40	37	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
3	72	63	57	51	61	54	49	37	34	31	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
4	65	56	48	43	56	48	42	33	29	26	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
5	60	49	42	36	51	42	36	29	25	22	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
6	55	44	36	31	47	38	32	26	22	19	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
7	50	39	32	27	43	34	28	23	19	17	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
8	47	35	28	23	40	30	24	21	17	14	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
9	43	32	25	20	37	27	22	19	15	13	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
10	40	29	22	18	34	25	19	17	14	11	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0

Avg. Luminance (cd/m2)

Vertical Angle	Horizontal Angle		
	0	45	90
55	0	0	0
65	0	0	0
75	0	0	0
85	0	0	0

Distribution

Hemisphere	100% Up / 0% Down
Peak/Zenith	2.40
Peak Output	2106 cd
Glare Control	Meets RP-1-12 recommendations for VDT-Critical spaces

LED

lighting facts®

A Program of the U.S. DOE

Philips Ledalite

Light Output (Lumens)

4765

Watts

41

Lumens per Watt (Efficacy)

116.22

Color Accuracy

Color Rendering Index (CRI)

82

Light Color

Correlated Color Temperature (CCT)

3434 (Bright White)

Warm White

Bright White

Daylight

2700K

3000K

4500K

6500K

All results are according to IESNA LM-79-2008: Approved Method for the Electrical and Photometric Testing of Solid-State Lighting. The U.S. Department of Energy (DOE) verifies product test data and results.

Visit www.lightingfacts.com for the Label Reference Guide.

Registration Number: F46Z-PYH3GQ (1/27/2015)

Model Number: 29x3LBCNQ

Type: Luminaire - Linear

TruGroove Suspended

4800 lm/4ft, Indirect
3000/3500/4000K

Optical Performance

Nominal CCT:	3000K	3500K	4000K
Flux (lm)	4673	4765	4856
Efficacy (lm/W)	114.8	116.2	118.4
Power (W)	40.7	41.0	41.0
CCT (K)	3110	3434	4075
CRI	81	82	83
R9	3	6	13
x	0.4315	0.4114	0.3778
y	0.4063	0.3986	0.3770
Duv	0.0020	0.0020	0.0010

Electrical Performance - 3500K

Input Voltage	120V	277V	347V
Input Power	41.0W	40.1W	35.4W
Input Current	0.34A	0.15A	0.11A
Power Factor	0.998	0.977	0.967
Total Harm. Distortion	4.8%	11.9%	9.0%
Tested values . contact technical support for rated values. Off-state power zero unless certain controls are specified.			

