


1081/1004ICN
Lytecaster™
Convertible IC/Non-IC



1081/1004ICS
Lytecaster™ Remodeler
Convertible IC/Non-IC

Complete fixture consists of Reflector Trim & Frame-in Kit. Select each separately

Reflector Trim	Frame-in Kit	Installation Type	Lamp	Height
1081WH	1004ICN	5" IC	75W PAR30 outdoor rated*	7-1/2" (191mm)
Gloss White	1104ICRS	5" IC Remodeler	75W PAR30 outdoor rated*	7-1/2" (191mm)
1081CD	1004ICN	5" Non-IC	75W PAR30 outdoor rated*	7-1/2" (191mm)
Clear Diffuse	1004ICRS	5" Non-IC Remodeler	75W PAR30 outdoor rated*	7-1/2" (191mm)

* For safe operation, you must use Sylvania outdoor rated lamp.

Features

Reflector: Formed aluminum, .040" thick (18 ga); Gloss White and Clear Diffuse finish.

Frame-in Kit: See frame-in Kit specification sheet for more details.

Gasket: Flexible, high temperature silicone gasket ensure sealing of electrical components.

Accessories

LFG 356 - Replacement Gasket

Markings

cULus listed, suitable for wet locations. - Covered Ceiling Only, I.B.E.W.

Job Information	Type:
Job Name:	
Cat. No.:	
Lamp(s):	
Notes:	