codes and standards

- ETL Listed to UL Standard 924
- NFPA 101 (Life Safety Code)
- NFPA 70 (National Electric Code)
- Low profile meets ADA specifications on lighting fixtures

construction

- · Flame rated, UV stable ABS thermoplastic housing.
- · Units are available in a white finish only.
- Lenses are constructed of a high impact resistant polycarbonate material.

installation

- Snap together quick mount design.
- · Unit can be wall or ceiling mounted.
- Unit mounts up to a standard 4" square or octagon outlet box.

electronics Xtest

- All units utilize a microprocessor and contain the Xtest self-diagnostic/self-test circuitry.
- Each unit includes low voltage disconnect, AC lockout, and brownout protection.
- Each unit with Xtest circuitry will automatically conduct a self-test once a month with the lamps on to verify all systems are functioning properly. For complete details regarding Xtest circuitry see spec sheet CE-17050.
- 120/277VAC selectable input.
- Power Consumption: 6.12 Watts (.051 mA) @ 120V, 6.37 Watts (.023 mA) @ 277V.

lamps

 Standard units contain two 6 volt, 5 Watt MR11 halogen lamps which are adjustable.

battery

- 6V maintenance free sealed lead acid battery.
- Operating temperature range is 65°F (19°C) to 85°F (30°C).
- Provides a minimum of 90 minutes emergency illumination.

warranty

· Five year warranty on unit (lamps not included).

CM-22050

Commercial Emergency

CFX6 Series

Compac® Fixed Lens Thermoplastic Emergency Unit with **Xtest**





Specifier's Reference

Project

Туре

Model No.

Comments

Green Product Choice: CFX6

Catalog Number	Volts	Total Wattage	Housing Color	LampType
Lead Calcium:				
CFX6	6	12	White	5W MR11

Accessories (Order Separately)

WG3 -Wire Guard

PCS1 — Polycarbonate Vandal Shield



Xtest testing specifications

- Automatic Test: The system charger and lamps are continually being controlled via pre-determined parameters specific to each model configuration, automatically. The battery is controlled via a true open circuit test each hour after initial installation. One each month the Xtest System illuminates lamps under load for 30 minutes, simulating a power outage with a true charger off condition, without affecting long term battery life. This is above and beyond the requirements of the National Fire Protection Association. This gives you unequaled control and confidence, knowing you are meeting self-test code requirements each and every month.
- Manual Test: A manual test switch allows for the Xtest system to perform the following tests at any time:
 Press Button

Once-5 second test, charger off, no load


Twice-60 second test, charger off, lamps on

Three-90 minute test, charger off, lamps on

6-Second Hold-Fully reinitializes micro-processor.

Pressing once during any test will cancel/abort testing.

Xtest Status Indicator Panel



Location of sensor for laser activation of manual test via handheld remote laser tester (this is an optional feature, specify "LX" option)

Fault Indications:

Four LED indicators provide visible indication of system status:

AC/Green	Charger/Red	Batt/Red	Lamp/Red	Status/Fault	Action
On				AC power is on/OK	None
F				Performing Test	None
On	F	F	F	Lamp/Battery Disconnected or Charger Fault	Check connections; if ok, replace circuit board
On	F			Charger fault	Replace circuit board
On		F		Battery disconnected/fault	Check connection or replace battery
On			F	Lamp disconnected/bad or remote disconnected	Check connection then press manual test once to determine bad lamp/replace lamp or check remote lamp.*

On=Steady


F=Flashing


Blank=Off

*If unit has remote capacity and remote cable is connected to charger board but not connected to a remote load, then either connect remote load or disconnect cable from charger board.


performance

Meets Life Safety Code standard minimum illuminance of 0.1 FC and average illuminance of 1.0 FC. Assumes open space with no obstructions, mounting height: 8', ceiling height: 9', and reflectances: 80/50/20. Analysis based on independently tested photometrics.





dimensions



© 2016 Philips Lighting Holding B.V. All rights reserved. Philips reserves the right-make changes in specifications and/or-discontinue any product at any time without notice or obligation and will not be liable for any consequences resulting from the use of this publication. philips.com/luminaires



Philips Lighting North America Corporation 200 Franklin Square Drive, Somerset, NJ 08873 Tel. 855-486-2216

Philips Lighting Canada Ltd. 281 Hillmount Rd, Markham, ON, Canada L6C 2S3 Tel. 800-668-9008

11-1/16" (280.9mm