


GreenSpace Gen4 Downlight/LED 筒灯



Mounting instruction/ 安装说明

4441 000 97551



Type Number 产品型号	LEDs 颗粒数	Power 功率	Voltage 电压	Frequency 频率	
DN290B 1xDLED / ALU	9	6.9W	220-240V	50/60 Hz	0.275 / 0.335
DN291B 1xDLED / ALU	14	11.5W	220-240V	50/60 Hz	0.375 / 0.5
DN292B 1xDLED / ALU	20	16.4W	220-240V	50/60 Hz	0.5 / 0.75
DN293B 1xDLED / ALU	28	22.3W	220-240V	50/60 Hz	0.5 / 0.75

Dimension 灯具尺寸	A (mm)	B (mm)
DN290B 1xDLED / ALU	95 / 99	Φ 122
DN291B 1xDLED / ALU	105 / 109	Φ 167
DN292B 1xDLED / ALU	114 / 118	Φ 218
DN293B 1xDLED / ALU	114 / 118	Φ 218



I

a

b





Type/型号	Cut-out/开孔尺寸
DN290B	105~110mm
DN291B	150~155mm
DN292B	200~205mm
DN293B	200~205mm

2

a

b





Inrush Current

	DN290B	DN291B	DN292B	DN293B
Ipeak (A)	12	11	9	10
Twidth (µs)	2	3	26	28
MCB	Max. Luminaire No.			
Type B 16A	30	30	15	15
Type C 16A	50	50	25	25

- !
- The luminaire shall be installed by a qualified electrician and wired in accordance with the latest IEE electrical regulations or the national requirements.
灯具应由有资格的电工安装，接线要符合IEE 电气标准或国家标准。
 - The luminaire is complied to IEC 60598-1 ed.8 or GB 7000.1-2007.
此灯具是依据IEC60598-1 ed. 8 或国标GB 7000.1-2007所制造。
 - The luminaire shall, under no circumstance, be covered with insulation matting or similar material.
灯具不能被隔热衬垫或类似材料覆盖。
 - Do not switch on before complete installation.
接线过程中，切勿通电。
 - The light source of this luminaire is not replaceable; when the light source reaches its end of life the whole luminaire shall be replaced
灯具中光源不可更换，当灯具寿命终结时，请更换整个灯具。