



STREET SIDE



VERIFY BOLD LINE IS 7.5" LONG

(4) ANCHOR RODS
(SEE NOTE 4)

HAND HOLE THIS SIDE HOUSE SIDE



NOTES:

- SUGGESTED BOLT CIRCLE: 9 1/2" DIAMETER
MAXIMUM BOLT CIRCLE: 9 1/2" DIAMETER
MINIMUM BOLT CIRCLE: 7 1/2" DIAMETER
- HADCO STRONGLY RECOMMENDS USING LEVELING NUTS TO MOUNT THE POST BASE. IF FOUNDATION IS NOT LEVEL, INCREASE "X" DIMENSION ACCORDINGLY WHEN USING LEVELING NUTS WITH WASHERS.

X = 3" MINIMUM WITH LEVELING NUTS
X = 2" MINIMUM WITHOUT LEVELING NUTS
- IF USING GROUTING TO CONCEAL GAP BETWEEN BASE AND FOUNDATION, ALLOW FOR WATER DRAINAGE.
- ANCHOR ROD: MINIMUM: 3/4" DIAMETER
MAXIMUM: 1" DIAMETER

LG = 20" WHEN USING A 3/4" ANCHOR ROD
LG = 36" WHEN USING A 1" ANCHOR ROD

	<small>CONFIDENTIAL: This drawing is confidential and proprietary to Signify Holdings and may not be reproduced in whole or in part without the express written consent of Signify Holdings. © 2018 Signify Holdings. All rights reserved.</small>		TITLE: TEMP.AR,190
	<small>UNLESS OTHERWISE SPECIFIED: *ALL DIMENSIONS ARE IN INCHES. *ALL THREADS ARE UNC-2B OR UNF-2B AFTER COATING. *ALL THREADS ARE TO BE VERIFIED WITH A THREAD GAGE.</small>	DRAWN BY: M. N. BANKERT CHECKED BY: B. DORON APPR BY: E. HADDAD	DRW SIZE: C DATE: 3/5/97 DATE: 8/4/09 DATE: 3/6/97
<small>* DO NOT SCALE THIS DRAWING *</small>		EF-04-01-11 Rev.09 SCALE 1:1 SHEET 1 OF 1	PART NO: T01700451