


# PHILIPS ADVANCE

## High Pressure Sodium Lamp Ballast

Catalog Number 71A82J3  
For 250W S50  
60 Hz CWA  
Status: Active

### DIMENSIONS AND DATA

4 1/4 X 4 3/4 CORE - 2 COIL UNIT




INPUT VOLTS	230				
CIRCUIT TYPE	CWA				
POWER FACTOR (min)	90%				
REGULATION					
Line Volts	±10%				
Lamp Watts	WITHIN TRAPEZOID				
LINE CURRENT (Amps)					
Operating.....	1.31				
Open Circuit.....	0.90				
Starting.....	0.76				
UL TEMPERATURE RATINGS					
Insulation Class	H(180°C)				
Coil Temperature Code	1029				
MIN. AMBIENT STARTING TEMP.	-40°F or -40°C				
NOM. OPEN CIRCUIT VOLTAGE	188				
INPUT VOLTAGE AT LAMP DROPOUT.....	152				
INPUT WATTS	293				
RECOMMENDED FUSE (Amps).....	4				
CORE and COIL					
Dimension (A)	1.80				
Dimension (B)	3.40				
Weight (lbs.)	11				
Lead Lengths	12"				
CAPACITOR REQUIREMENT					
Microfarads	35.0				
Volts (min.)	240				
Fault Current Withstand (amps)					
60 Hz TEST PROCEDURES (Refer to Advance Test Procedure for HID Ballasts - Form 1270)					
High Potential Test (Volts)					
1 minute	2000				
2 seconds	2500				
Open Circuit Voltage Test (Volts)	170-205				
Short-Circuit Current Test (Amps)					
Secondary Current	3.70-4.50				
Input Current.....	0.50-0.80				

Capacitor: 7C350P24RA



Capacitance: 35  
Dia/Oval Dim: 1.65  
Height: 3.7  
Temp Rating: 105°C

Wiring Diagram:



Ordering Information

Order Suffix

Description

Ignitor: LI501-H4



Red (X1)  
White (X2)  
Blue (X3)

Ballast to Lamp Distance  
(BTL) = 5 feet  
Temp Rating: 105°C

Data is based upon tests performed by Philips Lighting Electronic N.A. in a controlled environment and representative of relative performance. Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.

Philips Lighting Electronic N.A.

10275 West Higgins Road · Rosemont, IL 60018 · Tel:800-322-2086 Fax:888-432-1882  
Customer Support/ Technical Service:800-372-3331 · OEM Support: 866-915-5886

06/14/12