

HADCO

by  Signify

Landscape

Transformer

TC152-12TP Inground transformer



Project: _____
Location: _____
Cat.No: _____
Type: _____
Lamps: _____ Qty: _____
Notes: _____

Ordering Guide

Example: TC152-12TP

Product Code	TC152-12TP Transformer
--------------	------------------------

Specifications

HOUSING:

Housing and cover are polyester powdercoated steel with removable door. Internal transformer is epoxy encapsulated. Exterior Mounting - Transformer should be mounted on the wall, structure, or post in the vertical position. Cable entries should be positioned downward.

ELECTRICAL ASSEMBLY:

The transformer is thermally protected and is shielded between the 120V input and the low voltage output, for safety. Insulation type transformers for safe operation. 6-ft heavy-duty 18-3 AWG, 105° C, SJT power cord with 3 prong grounded wall plug. Voltage control switch: Low = 11.5V, High = 12.5V. Euro-Board terminal block for easy low voltage cable attachment. Line voltage amperage draw: 150VA = .9AMP. Includes integral timer and photocell. 50/60Hz input. Consult factory for details.

CERTIFICATIONS:

ETL Listed to U.S. safety standards for wet locations. cETL listed to Canadian safety standards for wet locations. Manufactured to ISO 9001:2008 Standards.

WARRANTY:

Ten-year limited warranty.

Height :

11 1/4" (286mm)

Width:

3 1/2" (89mm)

Depth:

3 3/4" (95mm)

