



EU Declaration of Conformity

Manufacturer: Philips Lighting
 I.B.R.S./C.C.R.I. /Numéro 10461
 5600 VB Eindhoven, The Netherlands

Document No.: BG Prof - EU - OOP - 008b

Year in which CE Mark was first affixed: 2009

This declaration of conformity is issued under the sole responsibility of the manufacturer:

Product Range:	NAME: Zadora
	DESCRIPTION: Halogen based recessed luminaire
Product Code:	See Annex I

The designated products are in conformity with the following Union harmonization legislation and with the applicable requirements of the following harmonized standards:

Low Voltage Directive (LVD), 2014/35/EU	
EN 60598-1: 2015	Luminaires – General requirements and tests
EN 60598-2-2: 2012	Luminaires – Particular requirements – recessed luminaires

Electromagnetic compatibility Directive (EMC), 2014/30/EU	
EN 55015:2013/A1:2015	Limits and methods of measurement of radio disturbance characteristics of electrical lighting and similar equipment
EN 61000-3-2:2014	Limits for Harmonic emissions (<16A per phase)
EN 61000-3-3:2013	Limits. (Limitation of voltage changes, voltage fluctuations and flicker in public low-voltage supply systems, for equipment with rated current ≤
EN 61547:2009	Equipment for general lighting purposes – EMC immunity requirements

EcoDesign requirements for energy-related products Directive (ErP), 2009/125/EC and applicable Implementing Measures	
Implementing Measure EC/1194/2012	

Restriction of the use of certain Hazardous Substances in electrical and electronic equipment Directive (RoHS), 2011/65/EU	
EN50581:2012	

and are produced under a quality scheme at least in conformity with ISO 9001 or CENELEC permanent documents.

17-01-18
 Eindhoven
 The Netherlands

Olaf von Bose
 Quality Manager
 BG Professional Europe
 Philips Lighting



EU Declaration of Conformity Annex 1

Document No.: BG Prof - EU - OOP - 008b

Specification of the products

12NC	EAN	Designation code	Remarks
9105 025 40318	87115 595 73076	QB5570 1xHAL-R40-50WGZ10 K 230V II ALU	
9105 025 38918	87115 595 73250	QB5570 1xHAL-MR50-45W 12V BR MAT	
9105 025 40018	87115 595 73045	QB5570 1xHAL-R40-50WGZ10 K 230V II WH	
9105 025 32018	87115 595 74240	QB5570 1xHAL-FR50-50W K ET WH	
9105 025 38018	87115 595 73205	QB5570 1xHAL-MR50-45W 12V BR WH	
9105 025 38318	87115 595 73236	QB5570 1xHAL-MR50-45W 12V BR ALU	
9105 025 38118	87115 595 73212	QB5570 1xHAL-MR50-45W 12V BR CR	