


Vaya LineBar LED 线条灯

BCX503/BCX506/BCX509/BCX512 Mono


Mounting instruction 安装说明书

0000 0000 0000




type 型号	LEDs	Input Current(A) 输入电流（安培）	Pmax(W) 功率（瓦）	L（mm） 长度（毫米）	
BCX503 LED-HB/RD 24V	16	0.09	2.1	308	0.15
BCX503 LED-HB/GN 24V	16	0.09	2.1	308	0.15
BCX503 LED-HB/BL 24V	16	0.09	2.1	308	0.15
BCX503 LED-HB/AM 24V	16	0.09	2.1	308	0.15
BCX503 LED-HB/CW 24V	16	0.09	2.1	308	0.15
BCX503 LED-HB/MW 24V	16	0.09	2.1	308	0.15
BCX506 LED-HB/RD 24V	32	0.18	4.3	606	0.30
BCX506 LED-HB/GN 24V	32	0.18	4.3	606	0.30
BCX506 LED-HB/BL 24V	32	0.18	4.3	606	0.30
BCX506 LED-HB/AM 24V	32	0.18	4.3	606	0.30
BCX506 LED-HB/CW 24V	32	0.18	4.3	606	0.30
BCX506 LED-HB/MW 24V	32	0.18	4.3	606	0.30
BCX509 LED-HB/RD 24V	48	0.27	6.4	903	0.45
BCX509 LED-HB/GN 24V	48	0.27	6.4	903	0.45
BCX509 LED-HB/BL 24V	48	0.27	6.4	903	0.45
BCX509 LED-HB/AM 24V	48	0.27	6.4	903	0.45
BCX509 LED-HB/CW 24V	48	0.27	6.4	903	0.45
BCX509 LED-HB/MW 24V	48	0.27	6.4	903	0.45
BCX512 LED-HB/RD 24V	64	0.35	8.5	1200	0.60
BCX512 LED-HB/GN 24V	64	0.35	8.5	1200	0.60
BCX512 LED-HB/BL 24V	64	0.35	8.5	1200	0.60
BCX512 LED-HB/AM 24V	64	0.35	8.5	1200	0.60
BCX512 LED-HB/CW 24V	64	0.35	8.5	1200	0.60
BCX512 LED-HB/MW 24V	64	0.35	8.5	1200	0.60


3



4




5



6

Power supply unit to be ordered separately
电源与灯具搭配表



Mono Type(PS100)	
N	Quantity
0.3m	46
0.6m	23
0.9m	15
1.2m	11

For Leader Cable:
1. Brown : +24V
2. Blue: Ground
3. Black: Don't use
4. Yellow&green: Don't Use



- This device complies with CE EMC directive 2004/108/EC, while using with adaptor (adaptor model: PS100/PS200), if used with improper adaptor,
 - this device may cause harmful interference,
 - this device may be influenced by any interference received.
 在使用指定电源型号(电源型号: PS100/PS200), 灯具已通过CE EMC参照 2004/108/EC, 如果使用其他的电源型号,
 - 灯具可能产生有害的电磁干扰,
 - 灯具可能受到外界的电磁干扰。
- The external flexible cable or cord of this luminaire cannot be replaced; if the

- cord is damaged, the luminaire shall be destroyed.
外部电源线不能被直接替换, 如果电线损坏, 灯具会连带损坏。
- Use IP20 grade connection boxes for the power supply cables to ensure a complete IP20 system.
必须使用IP20的接线盒。
- The connection box must comply with IEC60598.
接线盒必须符合IEC60598。
- The cable gland of connection box must be suitable for lum lead cable.
接线盒的进线接头必须和灯具提供的引出线相匹配。