






Project:		
Spec Type:		
Catalog No:	7705LxBAA	
Qty		
Line Notes:		

Incredible efficacy & boundless lighting choices mean the re-engineered Sona suspended LED is destined to become a future classic. Flexible up/down distributions and tailored LED optics mean you always have the right light for every task.

Ordering guide



^{*} Nominal values within a range. Down kits reduce output & efficacy. Consult photometry data for CRI, color temp, lumens & distribution of chosen configuration.

Mount Type Consult separate mounting spec sheet for mount type options: Ledalite Suspended Mounting Options Endcaps - Integrated Controls Please indicate with check mark. Response Daylight Single Zone (DS) SpaceWise DT Occupancy & Daylight Sensor (SZ)







[†] Not all wiring types are available with all configurations. Consult Philips Ledalite for a complete list of available options.

6100 lm/4ft 70% Up 3000/3500/4000K

Optical System

 $\label{light Chamber Upper: Lateral-facing LED arrays deliver light into both the upper and lower hemispheres, giving a highly efficient, native 70% up / 30% down distribution with a wide, homogeneous upper batwing distribution. A fully indirect version with a solid lower housing can be specified, as well as a 50% down-light kit option.$

1 Light Chamber Lower: A downward-facing LED array aims light into the lower hemisphere, for a highly efficient, fully direct distribution or optional 80% down version.

2 Light Chambers: Both lateral-facing and downward-facing LED arrays are combined in separate upper and lower chambers for the ultimate in up/down distribution control

Lenses: On the upper surface an engineered diffuser smooths the light distribution on the ceiling and acts as a dust cover. On the lower surface, two 4" wide optics are available: either a curved, engineered acrylic diffuse lens flush to the housing; or a white louver with regressed diffuser for improved high angle cut-off and visual comfort.

Endcaps

Diecast aluminum endcaps, either Sculpted (curved) or Flat

Finish

High quality powder coated, available in matte white, black or titanium silver. Other custom colors, including pacific aqua, are available on request. White sensors only.

Housing

Precision formed 18 gauge cold-rolled steel. Cross section size (approx.): $2.6\,^{\rm h}$ x $9\,^{\rm w}$ (suspended) or $7.4\,^{\rm w}$ (wall mount).

Weight

Maximum: Suspended 4.9lb/ft, Wall 3.4lb/ft

Electrical

Factory pre-wired to section ends with quick-wire connectors.

Standard Drivers

Philips Advance Xitanium 0-10V, 1-100%. Philips Advance Xitanium Sensor Ready, 5-100%. Class 2 rated output. Consult Philips Ledalite for other available drivers.

Standard Battery Pack

Philips Bodine, 90 min, 10W, Class 2 rated output, Emergency lumen output = 10W x luminaire efficacy x 1.1. Typical output: suspended 1400lm, wall 1200lm.

Lumen Maintenance

LEDs have been tested by the manufacturer in accordance with IESNA LM-80-08. At an ambient temperature of 25°C, the LED lumen maintenance expectation according to IES TM-21-11 is: L_{80} (12k) >72,000 hrs (**Reported** methodology) L_{80} (12k) 110,000 hrs (**Projected** methodology).

Source Color

LEDs rated for color rendering CRI >80, R9 >0 and fixture to fixture color accuracy within 3 SDCM.

Controls

Suspended version (1 light chamber only) available with the following integrated controls: Response Daylight Sensors SpaceWise DT Occupancy & Daylight Sensors w/ advanced grouping & Dwell Time.

*SpaceWise DT commissioning is via a compatible Android phone and Philips Field App. Compatible wireless dimming wall switches are available for dimming. 347V is not available as a standard option. For more information, please refer to www.philips.com/spacewise

Mounting

Suspended: Rapid installation sling mount at joints and ends. High strength aircraft cable and stainless steel gripper provide unlimited vertical adjustment and are independently tested to stringent safety standards. Variable mounting along the length of the housing is available for certain configurations upon request. Wall: A hidden steel rail and bracket system attaches to the existing structure and supports housings close to the wall. Mount positioning is fully variable along the modules to accommodate site conditions, spaced up to 4½' on center and within 6" of an end or joint.

Joints

Self-aligning, gasketed joining system with hands-free wiring feature.

Approvals

Certified to UL, CSA and IES standards. Most suspended versions (except 1 light chamber down with louver) are DesignLights Consortium® qualified. Please see the DLC QPL list for exact catalog numbers (www.designlights.org/QPL).

Warranty


Philips indoor professional luminaires 5 year LED warranty: www.philips.com/warranties

Environment

Rated for dry or damp locations in operating ambient temperatures 0-40°C (32-104°F). Certain luminaire components may be adversely affected by contaminants. Damage caused by sulfur, chlorine, petroleum based solutions or other contaminants in the area of operation are not covered under warranty. Not suitable for natatorium environments.

Due to continuing product improvements, Philips Ledalite reserves the right to change the specifications without notice.


Dimensions - Cross Section




6100 lm/4ft 70% Up 3000/3500/4000K

Dimensions - Modules

Suspended - Side view, no end caps




Optics and Styles




6100 lm/4ft 70% Up 3000/3500/4000K

Photometry @ CRI>80, 3500K



68% Up / 32% Down



Candela Distribution

Vertical		Но	rizontal /	Angle		Zonal
Angle	0	22.5	45	67.5	90	Lumens
0	657	657	657	657	657	0
5	650	656	655	653	653	62
15	629	634	636	635	635	179
25	586	591	596	600	601	274
35	521	529	539	541	540	335
45	440	449	461	459	460	351
55	344	357	362	362	364	320
65	236	247	252	256	259	248
75	125	134	145	153	158	152
85	31	46	62	75	79	67
90	2	20	36	49	56	0
95	55	73	106	113	112	112
105	186	256	362	430	456	367
115	315	503	760	917	967	696
125	428	718	1105	1335	1406	898
135	502	764	1127	1350	1416	810
145	550	735	1016	1195	1253	605
155	584	691	877	1007	1050	394
165	603	648	735	803	829	208
175	612	622	633	643	651	62
180	618	618	618	618	618	0

Values per 4ft unit

Fixture photometry has been conducted in accordance with IESNA LM-79-08

IES files for this and other photometric options can be downloaded online at www.lightingproducts.philips.com

Coefficients of Utilization (%)

ncn	Ceiling:		8	0			70			50		0
RCR	Wall:	70	50	30	10	70	50	30	50	30	10	0
0		103	103	103	103	93	93	93	74	74	74	32
1		94	89	85	82	84	80	77	64	62	60	27
2		85	78	71	66	76	70	65	56	52	49	22
3		77	68	61	55	69	61	55	49	45	41	18
4		71	60	52	46	63	54	47	43	38	35	16
5		65	53	45	39	58	48	41	39	33	30	13
6		59	48	40	34	53	43	36	35	29	26	12
7		55	43	35	29	49	39	32	31	26	22	10
8		51	39	31	26	46	35	28	28	23	20	9
9		47	35	28	23	42	32	25	26	21	18	8
10		44	32	25	20	39	29	23	24	19	16	7

Avg. Luminance (cd/m2)

Vertical	Honzontal Angle				
Angle	0	45	90		
55	5382	5360	5295		
65	5002	4911	4916		
75	4270	4307	4507		
85	2983	4176	4878		

Distribution

Hemisphere	68% Up / 32% Down
Peak/Zenith	2.35
Peak Output	1453 cd

6100 lm/4ft 70% Up 3000/3500/4000K

Optical Performance @ 120V

Nominal Spec:	3000K	3500K	4000K
Flux (lm)	5899	6142	6273
Efficacy (lm/W)	130.2	135.6	137.6
Power (W)	45.3	45.3	45.6
CCT (K)	3020	3378	3958
CRI	84	83	84
R9	11	9	11
x	0.4361	0.4138	0.3835
у	0.4048	0.3976	0.3820
Duv	0.0003	0.0012	0.0016

Electrical Performance @ CRI>80, 3500K

Input Voltage	120V	277V	347V
Input Power	45.3W	44.8W	45.4W
Input Current	0.38A	0.17A	0.13A
Power Factor	0.995	0.971	0.987
Total Harm. Distortion	6.8%	10.5%	8.0%

Tested values – contact technical support for rated values. Off-state power zero unless certain controls are specified.

With SpaceWise DT, standby power <0.5W (120V) or <0.8W (277V).

