

codes and standards

- UL 924 listed

construction

- Constructed of durable die cast aluminum.
- Available in black or bronze.

installation

- CEF Series has single or double mounting plates available.

lamps

- 12 V, 20, 35 or 50 W MR16 halogen lamps available.
- CEF Series is available with a 12 V, 7 W MR16 LED lamp option.
- CEF Series, lamps included unless specified otherwise.

CA-51050

Remotes

CEF Series

12 V MR16 Outdoor
Remote Lamp Heads



Specifier's Reference

Project

Type

Model No.

Comments

Model Example: CEF1RBZ20WF

CEF

Series

CEF – Decorative
Outdoor
Remote Head

of Heads

1 – Single Remote Head
2 – Double Remote Head

Type of Mounting Plate

R – 4" Round Mounting Plate
S – Single Gang Rectangular Mounting Plate

Color

BK – Black
BZ – Bronze

Lamp Type

MR16 Halogen Lamps
Blank – No Lamps Installed
20WF – 12 V, 20 W Wide Flood 40°
35FL – 12 V, 35 W Flood 25°
35WF – 12 V, 35 W Wide Flood 40°
50FL – 12 V, 50 W Flood 25°
50WF – 12 V, 50 W Wide Flood 40°

Accessories (Order Separately)


ORBBK – Outdoor 4" Round Surface Mount Junction Box, Black
ORBBZ – Outdoor 4" Round Surface Mount Junction Box, Bronze
OSBBK – Outdoor Single Gang, Surface/Recessed 2-3/4" x 4-1/2" Junction Box, Black
OSBBZ – Outdoor Single Gang, Surface/Recessed 2-3/4" x 4-1/2" Junction Box, Bronze

MR16 LED Lamp
7F – 12 V, 7 W Flood 35°


PHILIPS
CHLORIDE

dimensions


single CEF with round mounting plate




double CEF with round mounting plate




single CEF with rectangular mounting plate



double CEF with rectangular mounting plate



junction boxes for CEF
ORBBZ



OSBBZ

