



Project: _____
 Location: _____
 Cat.No: _____
 Type: _____
 Lamps: _____ Qty: _____
 Notes: _____

FAEM1T
 FAEM2T
 FAEM3E

Compatibility Matrix				Lumen Output with Battery Pack		
Lamp	Base	Ballast	Specify	1-Light Fixture	2-Light Fixture Both Lamps On	2-Light Fixture One Lamp On
13W Quad, 4-pin	G24q-1	Electronic	FAEM3E	350	425	---
			FAEM4E	350	400	---
18W Quad, 4-pin	G24q-2	Electronic	FAEM3E	475	575	---
			FAEM4E	350	550	---
26W Quad, 4-pin	G24q-3	Electronic	FAEM3E	600	700	---
			FAEM4E	425	---	425
18W Triple, 4-pin	GX24q-2	Electronic	FAEM3E	300	525	---
			FAEM4E	350	550	---
26W Triple, 4-pin	GX24q-3	Electronic	FAEM3E	450	725	---
			FAEM4E	425	---	425
32W Triple, 4-pin	GX24q-3	Electronic	FAEM3E	575	750	---
			FAEM4E	600	---	600
42W Triple, 4-pin	GX24q-4	Electronic	FAEM3E	750	---	750
			FAEM4E	750	---	750

FAEM3E is only compatible to wire both lamps on up to 2-32W.
 FAEM4E is only compatible to wire both lamps on up to 2-18W.

Features

General Description: Accessory Kit attaches in the field to standard compact fluorescent downlights to provide emergency downlighting from readily available modular components.

- Battery Pack:** Provides 90 minute emergency lighting when AC power fails. Fully encased, long-life nickel cadmium; may be replaced from below; charges from 120 and 277VAC. Meets National Electrical and Life Safety Codes.
- Battery Pack Support Bracket:** Snaps onto Frame-In Kit mounting bracket.
- Stab-In Connectors:** Ballast and lamp leads stab into quick connector simplifying installation and service.

Features (cont.)

- Test Switch and Charge Light:** (FAEM1T, FAEM2T, FAEM3E) Included in easy-to-install recessed switch box. May be remoted to closet or cabinet (up to 50' away) if desired. Matte white, 4 1/2" diameter canopy.
FAEM4E Includes one piece test switch and charge light with 2 3/4" dia. matte white cover plate; installs in ceiling or in optional reflectors (consult factory).
- Frame-In Kit/Reflector Trim:** Use standard Calculite compact fluorescent Frame-In Kit and Reflector Trim as desired.

Labels

UL Listed for indoor dry locations. Not approved for Chicago Plenum

