

PHILIPS ADVANCE

Metal
Halide
Lamp Ballast

Catalog Number 71A60H1A
For 400W M59
60 Hz CWA
Status: Active

DIMENSIONS AND DATA

4 1/4 X 4 3/4 CORE - 2 COIL UNIT



| | | | | | |
|--|----------------|-----------|---|---|---|
| INPUT VOLTS | 127 | 220 | | | |
| CIRCUIT TYPE | CWA | | | | |
| POWER FACTOR (min) | 90% | | | | |
| REGULATION | | | | | |
| Line Volts | ±10% | | | | |
| Lamp Watts | ±10% | | | | |
| LINE CURRENT (Amps) | | | | | |
| Operating..... | 3.90 | 2.20 | | | |
| Open Circuit..... | 3.11 | 1.80 | | | |
| Starting..... | 2.74 | 1.56 | | | |
| UL TEMPERATURE RATINGS | | | | | |
| Insulation Class | H(180°C) | | | | |
| Coil Temperature Code | 1029 | | | | |
| | F | F | | | |
| MIN. AMBIENT STARTING TEMP. | -20°F or -30°C | | | | |
| NOM. OPEN CIRCUIT VOLTAGE | 300 | | | | |
| INPUT VOLTAGE AT LAMP DROPOUT..... | 64 | 110 | | | |
| INPUT WATTS | 454 | | | | |
| RECOMMENDED FUSE (Amps)..... | 10 | 7 | | | |
| CORE and COIL | | | | | |
| Dimension (A) | 2.14 | | | | |
| Dimension (B) | 4.05 | | | | |
| Weight (lbs.) | 11.4 | | | | |
| Lead Lengths | 12" | | | | |
| CAPACITOR REQUIREMENT | | | | | |
| Microfarads | 24.0 | | | | |
| Volts (min.) | 400 | | | | |
| Fault Current Withstand (amps) | | | | | |
| 60 Hz TEST PROCEDURES (Refer to Advance Test Procedure for HID Ballasts - Form 1270) | | | | | |
| High Potential Test (Volts) | | | | | |
| 1 minute | 2000 | | | | |
| 2 seconds | 2500 | | | | |
| Open Circuit Voltage Test (Volts) | 270-330 | | | | |
| Short-Circuit Current Test (Amps) | | | | | |
| Secondary Current | 3.50-4.30 | | | | |
| Input Current..... | 2.45-3.90 | 1.40-2.20 | - | - | - |

Capacitor: 7C240P40-R



Capacitance: 24
Dia/Oval Dim: 1.75
Height: 4.8
Temp Rating: 105°C

Wiring Diagram:




Fig. M8

Ordering Information

| Order Suffix | Description |
|--------------|-------------|
| | |

Ignitor: NA

NA

This ballast does not require the use of an ignitor.

Data is based upon tests performed by Philips Lighting Electronic N.A. in a controlled environment and representative of relative performance. Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.

Philips Lighting Electronic N.A.

10275 West Higgins Road · Rosemont, IL 60018 · Tel:800-322-2086 Fax:888-432-1882
Customer Support/ Technical Service:800-372-3331 · OEM Support: 866-915-5886

10/18/11