


GreenPerform Highbay II 飞利浦LED高天棚灯

BY688P LED160 /BY689P LED100

Mounting instruction / 安装说明书

444170095041




产品名称 Description	色温 Color	配光 Optics	重量 Weight	系统功率 Wattage
BY688P LED160/CW PSU S-WB	CW	WB	7kg	160W
BY688P LED160/CW PSU S-NB		NB		
BY688P LED160/CW PSU S-HRO		HRO		
BY688P LED160/NW PSU S-WB	NW	WB		
BY688P LED160/NW PSU S-NB		NB		
BY688P LED160/NW PSU S-HRO		HRO		
BY689P LED100/CW PSU S-WB	CW	WB	5kg	100W
BY689P LED100/CW PSU S-NB		NB		
BY689P LED100/CW PSU S-HRO		HRO		
BY689P LED100/NW PSU S-WB	NW	WB		
BY689P LED100/NW PSU S-NB		NB		
BY689P LED100/NW PSU S-HRO		HRO		

安装附件/Mounting accessories

- 挂钩组件/Mounting hook
a. Hook
- 支架组件/Mounting bracket
a. BY618Z MB
b. BY619Z MB


Dimensions 尺寸

Type 型号	Dimension 尺寸(mm)		
	D	W	H
BY688P	Φ457	466	158
BY689P	Φ366	374	153





1 Installation 安装应用

Hook mounting/吊装





Pipe mounting/杆装



Pipe dim.
铁管尺寸


Bracket mounting/支架安装



Mounting hole
安装孔位

2 Connect entry cable 连接电源线

Please use IP65 or above waterproof terminal block, it is not provided by Philips.
请使用IP65以上的接线盒(接线端子尺寸不小于10x20x25mm),飞利浦不提供接线盒。



Cable:
60227IEC53 3x1.0~1.5mm²
60245IEC57 3x1.0~1.5mm²

外部3芯线定义如下:
棕Brown - L
黄绿YellowGreen - G
蓝Blue - N



- The luminaire shall be installed or maintained By a qualified electrician and wired in accordance with the latest IEE electrical regulations or the national requirements.
灯具应由有资格的电工安装或维修, 接线要符合IEE 电气标准或国家标准。
- The luminaire shall, under no circumstance, be covered with insulation matting or similar material.
灯具不适合被隔热或类似材料覆盖。
- The cable of the luminaire should use "Y" type connection. It should be maintained by professional electrician.
灯具电源线使用Y型连接, 电源线损坏需专业人士更换。
- For metal structures, make sure adequate insulation is used for the mounting.
金属结构必须做好绝缘安装。