


GB/T 1804-2000m (Unit: mm)																	
SIZE RANGE		0.5-3		>3-6		>6-30	>30-120	>120-400	>400-1000								
TOLERANCE		±0.1		±0.1		±0.2	±0.3	±0.5	±0.8	ITEM		ASSEMBLY NO.		QUANT.			
GENERAL ROUGHNESS <div>✓</div>		UNIT		MATERIAL													
		mm															
SCALE		PROJECT TYPE 		TREATMENT										ORDER NO.		QUANT.	
				TITLE: Dimensional Sketch LRI1655-00 ACTILUME 1-10V SENSOR 100 CM						PART NUMBER: 9137 003 39500		2010/7/7 B					
REV. CHANGE NO.		DATE															
DESIGNED BY		Yugui Xu		CHECKED BY			1		SH.		SH. 112 of 1		FORM NO.		A3		
DRAWN BY				APPROVED BY			REVISED BY		PHILIPS LIGHTING ELECTRONICS (SHANGHAI) CO., LTD.								