

PHILIPS
LIGHTOLIER

Downlighting

Calculite LED

Round aperture
Vandal proof trim



Experience the change, **see the difference**

Philips Lightolier Calculite LED generation 3

architectural decorative vandal proof ring combines the impact resistance you need with aesthetics you want.

Calculite's vandal proof trim accessory is strength with a decorative feel. The sleek machined aluminum ring provides aesthetics fit for architectural spaces while providing the rigidity and impact resistance needed for the most demanding applications. The solid aluminum construction with clear polycarbonate lens lock in place to deter tampering, and provide Calculite trims with an IK10 impact rating.

Calculite LED gen 3

Vandal proof trim

Features

- **Apertures:** 4", and 6" round.
- **Finish:** White.
- **Reflectors:** Suitable for use with any finish. Must use flangeless trim option.
- **Lumen packages:** 4" in 500lm to 3000lm; 6" in 1000lm to 6000lm.
- **Construction:** Machined alluminum. 9034HO Lexan optical grade polycarbonate lens.
- **Impact Protection Rating:** IK10 (protected against 20 joule impact)*
- **Ingress Protection Rating:** IP65, suitable for wet locations.
- **Locking:** Vandal proof trim locks in place with discrete setscrew located on side of the ring.
- **Installation:** Mounted to frame with hardware, bayonet style twist on trim installation.




* Impact Protection Rating is a scale of 0-10 used to measure a product's ability to withstand physical impact.

Frame

example: C4RN

Series	Aperture	Installation	Voltage / Options
	R		
C4 Calculite LED 4" aperture	R Round	N New construction	— Universal (120/277V) 3 347V EM Emergency LC Chicago Plenum
C6 Calculite LED 6" aperture		R Remodeler	
		A AirSeal IC (120/277V)	—

Vandal proof 4" & 6 accessory (VP)



Engine

example: C4L15835NZ10U

Series	Lumens	CRI	CCT	Beam	Dimming	Options
						U
C4L Calculite LED 4" aperture	05 500lm	8 80CRI 9 90CRI	27 2700K 30 3000K 35 3500K 40 4000K	N Narrow M Medium W Wide	Z10 0-10V 1% D Dali L Lutron EcoSystem	U Universal (120/277/347V)
	10 1000lm					
	15 1500lm					
C4L Calculite LED 4" aperture	20 2000lm	8 80CRI 9 90CRI	27 2700K 30 3000K 35 3500K 40 4000K	N Narrow M Medium W Wide	Z10 0-10V 1% D Dali L Lutron EcoSystem	U Universal (120/277/347V)
	25 2500lm					
	35 3500lm					
	48 4800lm					
	60 6000lm					

Trim

example: C4RDLCCF

Series	Aperture	Style	Finish	Flange
C4 Calculite LED 4" aperture	R Round	DL Downlight	CL Specular clear	F Flangeless
C6 Calculite LED 6" aperture		WW Open Wall Wash	CC Comfort clear	
		LW Lensed Wall Wash	CD Comfort clear diffuse	
		CW Corner Wall Wash	CZ Champagne bronze	
		DW Double Wall Was	BK Black (matte)	
			WH White (matte)	



Note: Prior to ordering, consult specification sheets on www.philips.com/luminaires for the most current information, notes, and exclusions.

© 2017 Philips Lighting Holding B.V. All rights reserved.
Philips reserves the right to make changes in specifications and/or to discontinue any product at any time without notice or obligation and will not be liable for any consequences resulting from the use of this publication.



Philips Lighting North America Corporation
200 Franklin Square Drive, Somerset, NJ 08873
Tel. 855-486-2216

Philips Lighting Canada Ltd.
281 Hillmount Rd, Markham, ON, Canada L6C 2S3
Tel. 800-668-9008