

# Linear

Sync Suspended

6500 lm/4ft w/ 55% Down Kit\* 3000/3500/4000K





Project:

Spec Type:


Catalog No: 7406LxAQD

Qty

Line Notes:

With its slim, uncluttered design, Sync is the epitome of compact style. Sync offers true direct/indirect lighting distribution and luminous aesthetics with exceptional glare control.

# Ordering guide



\* Nominal values within a range. Down kits reduce output & efficacy. Consult photometry data for color temp, lumens & distribution of chosen configuration.

† Not all wiring types are available with all configurations. Consult Philips Ledalite for a complete list of available options.

#### **Mounting Hardware**

		Suspension Length Distance from ceiling to top of luminaire in inches
Endcaps -		Integrated Controls Please indicate with check mark.
	Sculpted	Response Daylight Single Zone (DS)



# Sync Suspended

6500 lm/4ft w/ 55% Down Kit\* 3000/3500/4000K

### **Optical System**

The optical system contains arrays of LEDs edge–lighting a low profile light-guide panel, using total internal reflection to homogenize the sources. The microstructured surface of the panel optimizes light extraction to create an efficacious direct/indirect distribution. Light is purified and controlled by MesoOptics film as it passes through a non-glare acrylic lens. Standard distribution is 75% up / 25% down for suspended and 65% up / 35% down for wall mount version.

#### Endcaps

Diecast aluminum endcaps, available in flat (standard) or sculpted (optional).

#### Finish

Standard finish is a textured matte powder coat in white, black or titanium silver.

#### Housing

Precision formed 18 gauge cold-rolled steel.

#### Weight

Maximum: Suspended 3.75lb/ft & Wall 3.0lb/ft.

#### Electrical

Factory pre-wired to section ends with quick-wire connectors.

#### **Standard Driver**

Philips Advance Xitanium 0-10V, 1-100%. Class 2 rated output. Consult Philips Ledalite for other available drivers.

#### **Standard Battery Pack**

Philips Bodine, 90 min, 10W, Class 2 rated output, Emergency lumen output = 10W x luminaire efficacy x 1.1. Typical output: 1100lm.

#### Lumen Maintenance

LEDs have been tested by the manufacturer in accordance with IESNA LM-80-08. At an ambient temperature of 25°C, the LED lumen maintenance expectation according to IES TM-21-11 is:  $L_{80}$  (12k) >72,000 hrs (**Reported** methodology).

#### Source Color

LEDs rated for color rendering CRI >80 and fixture to fixture color accuracy within 2 SDCM.

#### Controls

Suspended version available with the following integrated controls: Response daylight sensor (for single zone).

#### Mounting

Suspended: Tamper-resistant aircraft cable gripper provides unlimited vertical adjustment. Aircraft cable, crimp and cable gripper are independently tested to meet stringent safety requirements. Wall: Fixture is mounted flush to wall using hidden wall brackets which attach to existing structure, variable within 2"-5" of end or joint.

#### Joints

Self-aligning joining system with hands-free pre-joining wire access.

#### **Approvals**

Certified to UL, CSA and IES standards. Certain suspended versions without down kits are DesignLights Consortium® qualified. Please see the DLC QPL list for exact catalog numbers (www.designlights.org/QPL).

#### Warranty


Philips indoor professional luminaires 5 year LED warranty: www.philips.com/warranties.

#### Environment

Rated for dry or damp locations in operating ambient temperatures 0-40°C (32-104°F). Certain luminaire components may be adversely affected by contaminants. Damage caused by sulfur, chlorine, petroleum based solutions or other contaminants are not covered under warranty. Not suitable for natatorium environments.

Due to continuing product improvements, Philips Ledalite reserves the right to change the specifications without notice.

# **Dimensions - Cross Section**




### **Dimensions - Modules**

#### Modules

Module length excludes end caps. Nominal mounting spacing for individually mounted modules.

J 100% Down Kit



Note: Refer to installation instructions for exact mount.

# **Optics and Styles**

#### Lens view

G 80% Down Kit

Suspended (without endcaps)	3' <sup>3</sup> /8"
← Comper optics	<b>5</b> 5/8

# Sync Suspended 6500 lm/4ft w/ 55% Down Kit\*


3000/3500/4000K

# Photometry - 3500K

# Candela Distribution

90	135 - 90 1400 cd
45	

44% Up / 56% Down



Photometric Testing of Solid-State Lighting. The U.S. Department of Energy (DOE) verifies product test data and results.

Visit www.lightingfacts.com for the Label Reference Guide.

Registration Number: F46Z-285XSS (10/31/2016) Model Number: 7406LBAQD Type: Luminaire - Linear

Vertical Angle	Horizontal Angle 0 22.5 45 67.5 90					Zonal Lumens
0	957	957	957	957	957	0
5	961	963	969	975	979	94
15	992	1008	1065	1119	1136	304
25	1020	1058	1176	1282	1322	539
35	967	1000	1097	1164	1188	670
45	752	748	758	760	760	585
55	491	479	475	479	483	434
65	290	288	292	300	306	291
75	118	122	124	128	128	136
85	22	24	26	28	28	31
90	0	0	0	0	0	0
95	53	67	99	132	146	133
105	231	288	410	584	693	450
115	324	387	533	698	787	532
125	343	393	499	620	671	452
135	331	363	424	481	499	328
145	326	341	379	401	401	234
155	328	333	353	363	361	162
165	326	326	331	333	333	94
175	316	316	316	316	316	30
180	314	314	314	314	314	0

Values per 4ft unit Fixture photometry has been conducted in accordance with IESNA LM-79-08 IES files for this and other photometric options can be downloaded online at www.lightingproducts.philips.com

# Coefficients of Utilization (%)

DCD	Ceiling:		8	0			70			50		0
RCR	Wall:	70	50	30	10	70	50	30	50	30	10	0
0		109	109	109	109	101	101	101	87	87	87	56
1		100	95	92	88	93	89	86	77	74	72	48
2		91	84	78	73	84	78	73	68	64	60	41
3		83	74	67	61	77	69	63	60	55	51	35
4		76	66	58	52	71	61	55	54	48	44	30
5		70	59	51	45	65	55	48	48	42	38	26
6		65	53	45	39	60	49	42	43	37	33	23
7		60	48	40	34	56	45	38	39	33	29	21
8		55	43	35	30	52	41	34	36	30	26	18
9		52	39	32	27	48	37	30	33	27	23	17
10		48	36	29	24	45	34	27	30	25	21	15

#### Avg. Luminance (cd/m2)

0		``	'
Vertical	H	orizontal Ang	gle
Angle	0	45	90
55	8311	8044	8177
65	6659	6704	7021
75	4438	4660	4808
85	2416	2855	3075

# Distribution

Hemisphere	44% Up / 56% Down		
Glare Control	None		
Spacing Along (0 °)	1.5		
Spacing Across (90 °)	1.62		

# Sync Suspended

6500 lm/4ft w/ 55% Down Kit\* 3000/3500/4000K

# **Optical Performance**

Nominal CCT:	3000К	3500К	4000K
Flux (lm)	5265	5499	5655
Efficacy (lm/W)	92.5	97.0	100.1
Power (W)	56.9	56.7	56.5
ССТ (К)	3045	3312	3931
CRI	84	82	83
R9	10	-1	5
x	0.4338	0.4167	0.3849
У	0.4031	0.3968	0.3837
Duv	0.0000	0.0000	0.0020

# Electrical Performance - 3500K

Input Voltage	120V	277V	347V		
Input Power	56.7W	56.2W	56.9W		
Input Current	0.47A	0.21A	0.17A		
Power Factor	0.995	0.987	0.970		
Total Harm. Distortion	9.4%	10.2%	11.0%		
Tested values . contact technical support for rated values. Off-state power zero unless certain controls are specified.					

© 2017 Philips Lighting Holding B.V. Il rights reserved. Philips reserves the right to make changes in specifications and/or to discontinue any product at any time without notice or obligation and will not be liable for any consequences resulting from the use of this publication. www.philips.com/luminaires



Philips Lighting, North America Corporation 200 Franklin Square Drive, Somerset, NJ 08873 Tel. 855-486-2216

Philips Lighting Canada Ltd., 281 Hillmount Rd, Markham, ON, Canada L6C 2S3 Tel. 800-668-9008