


Jump's contemporary aesthetic combines the latest lighting technologies with texture, pattern, and rhythm along an uninterrupted end to end continuum of luminance.

Ordering guide



* Nominal values within a range. Consult photometry data for color temp, lumens & distribution of chosen configuration.

F -Flat

† Not all wiring types are available with all configurations. Consult Philips Ledalite for a complete list of available options.

Mount Type
Consult separate mounting spec sheet for mount type options

Endcaps
Integrated Controls Please indicate with check mark.

Response Daylight Single Zone (DS)





S - Luminous Sculpted (standard)

2000 lm/4ft, Asymmetric Solid 3000/3500/4000K

Optical System

White light emitted from a linear array of downwardfacing LEDs is laterally redirected using either a biconvex lens or optical microstructures embedded in a layer of MesoOptics DX film. An extruded, ribbed acrylic lens and MesoOptics film assembly then generates an optimal batwing distribution and a uniform continuum of light.

Endcaps

Diecast aluminum, available in luminous sculpted (standard) or flat (optional).

Finish

High quality powder coated, available in matte white, black or titanium silver. Other custom colors available on request.

Housing

20 gauge cold-rolled steel, precision formed and welded with optional perforated patterns.

Weight

Maximum 3.5lb/ft.

Electrical

Factory pre-wired to section ends with quick-wire connectors.

Standard Driver

Philips Advance Xitanium 0-10V, 1-100%. Class 2 rated output. Consult Philips Ledalite for other available drivers.

Standard Battery Pack

Philips Bodine, 90 min, 10W, Class 2 rated output, Emergency lumen output = 10W x luminaire efficacy x 1.1. Typical output: symmetric 1300lm, asymmetric 1100lm.

Lumen Maintenance

At an ambient temperature of 25° C, the LED lumen maintenance expectation according to IES TM-21-11 is: L₈₀ (12k) >72,000 hrs (**Reported** methodology) L₇₀ (12k) 110,000 hrs (**Projected** methodology).

Source Color

LEDs rated for color rendering CRI >80, R9 >0 and fixture to fixture color accuracy within 2 SDCM.

Controls

Available with the following integrated controls: Response daylight sensor (for single zone).

Mounting

Variable position mounts can be installed up to 18" from each joint and end (suspended, surface, wall or cantilever). In the suspended mount, high strength aircraft cable and stainless steel gripper provide unlimited vertical adjustment and are independently tested to stringent safety standards.

Joints

Self-aligning joining system with hands-free pre-joining wire access.

Approvals

Certified to UL, CSA and IES standards. Certain symmetric versions (12x1L) excluding 3000K, 4900lm/4ft configurations (12x1LCC) are DesignLights Consortium® qualified. Please see the DLC QPL list for exact catalog numbers (www.designlights.org/QPL).

Warranty

Philips indoor professional luminaires 5 year LED warranty: http://www.philips.com/warranties

Environment

Rated for dry or damp locations in operating ambient temperatures 0–40°C (32–104°F). Certain luminaire components may be adversely affected by contaminants. Damage caused by sulfur, chlorine, petroleum based solutions or other contaminants in the area of operation are not covered under warranty. Not suitable for natatorium environments.


Due to continuing product improvements, Philips Ledalite reserves the right to change the specifications without notice.


Dimensions - Cross Section




2000 lm/4ft, Asymmetric Solid 3000/3500/4000K


Dimensions - Modules







Mounting Run Options









Optics and Styles









2000 lm/4ft, Asymmetric Solid 3000/3500/4000K

Photometry - 3500K



0% Up / 100% Down



Candela Distribution

Vertical			ontal Ar			Zona
Angle	0	45	90	135	180	Lumen
0	724	724	724	724	724	0
5	783	768	707	698	693	71
15	1025	903	686	677	703	224
25	1184	1018	650	675	699	376
35	966	889	597	599	577	442
45	572	564	460	422	375	370
55	315	308	286	257	226	252
65	172	163	155	146	129	153
75	81	74	69	70	62	76
85	9	13	18	21	16	20
90	0	0	0	0	0	0
95	0	0	0	0	0	0
105	0	0	0	0	0	0
115	0	0	0	0	0	0
125	0	0	0	0	0	0
135	0	0	0	0	0	0
145	0	0	0	0	0	0
155	0	0	0	0	0	0
165	0	0	0	0	0	0
175	0	0	0	0	0	0
180	0	0	0	0	0	0

Values per 4ft unit

Fixture photometry has been conducted in accordance with IESNA LM-79-08

IES files for this and other photometric options can be downloaded online at www.lightingproducts.philips.com

Coefficients of Utilization (%)

DCD	Ceiling:		8	80			70			50		0
RCR	Wall:	70	50	30	10	70	50	30	50	30	10	0
0		119	119	119	119	116	116	116	111	111	111	100
1		110	106	102	99	108	104	100	100	97	94	87
2		101	94	88	83	99	92	87	89	84	80	75
3		93	84	77	71	91	82	76	79	74	69	65
4		86	75	67	61	84	74	66	71	65	60	56
5		80	68	60	53	78	67	59	65	58	53	49
6		74	61	53	47	72	61	53	59	52	47	44
7		69	56	48	42	67	55	47	54	47	42	39
8		64	51	43	38	63	51	43	49	42	37	35
9		60	47	39	34	59	47	39	45	39	34	32
10		56	44	36	31	55	43	36	42	35	31	29

Avg. Luminance (cd/m2)

Vertical	H	orizontal An	gle
Angle	0	90	180
55	4589	4175	3295
65	3411	3060	2550
75	2631	2244	2010
85	826	1701	1510

Distribution

Hemisphere	0% Up / 100% Down
Glare Control	Meets RP-1-12 recommendations for VDT-Normal spaces
Spacing Along (0 °)	1.65
Spacing Across (90 °)	1.3
Spacing at 180 °	1.29

2000 lm/4ft, Asymmetric Solid 3000/3500/4000K

Optical Performance

Nominal CCT:	3000K	3500K	4000K
Flux (lm)	1892	1984	2013
Efficacy (lm/W)	96.0	101.2	101.7
Power (W)	19.7	19.6	19.8
CCT (K)	3076	3434	4055
CRI	84	83	84
R9	11	7	10
x	0.4321	0.4109	0.3792
у	0.4031	0.3974	0.3796
Duv	0.0002	0.0017	0.0018

Electrical Performance - 3500K

Input Voltage	120V	277V	347V	
Input Power	19.6VV	19.6W	20.7W	
Input Current	0.16A	0.07A	0.06A	
Power Factor	0.994	0.965	0.970	
Total Harm. Distortion	8.1%	11.7%	11.5%	

Tested values . contact technical support for rated values. Off-state power zero unless certain controls are specified.

