



TBS569

Installation Instruction


TBS569 - M001a



Basic Luminaire	Lamp Number/Watts	Gear	Optics
TBS569	2xTL-5 14W	EB-S	M2
	3xTL-5 14W		M5
	4xTL-5 14W	HF-A	M6
	2xTL-5 28W		C6
	3xTL-5 28W	EB-E	D6






Type	L	W	H	M	kg
TBS 569 2xTL-5 14W	597	297	55	8	1.8
TBS 569 3xTL-5 14W	597	597	55	8	3.6
TBS 569 4xTL-5 14W	597	597	55	8	3.8
TBS 569 2xTL-5 28W	1197	297	55	8	3.8
TBS 569 3xTL-5 28W	1197	597	55	8	7.8




Suspension via Hooks or Chains 钩式或链式悬挂安装

A





Only for with plug version 仅适用于带插头产品





Hanging via Bracket 支架安装

B-1



B-2



Rest steps same as suspension mounting 其余步骤同上



Attention: The luminaire shall, under no circumstances, be covered with thermal insulation matting or similar material.

注意事项：灯具不适合被 隔热垫或类似材料覆盖。