


PHILIPS ADVANCE

High Pressure Sodium Lamp Ballast

Catalog Number 74P7903
For 70W S62
60 Hz R-PFC
Status: Active

DIMENSIONS AND DATA



MAX. CASE TEMP 90°C

NIPPLE 1/2" NPT-14


POSTLINE UNIT DIMENSIONS

INPUT VOLTS	120				
CIRCUIT TYPE	R-PFC				
POWER FACTOR (min)	85%				
REGULATION					
Line Volts	±5%				
Lamp Watts	WITHIN TRAPEZOID				
LINE CURRENT (Amps)					
Operating.....	0.75				
Open Circuit.....	1.30				
Starting.....	1.60				
UL TEMPERATURE RATINGS					
Insulation Class	H(180°C)				
Coil Temperature Code	1029				
MIN. AMBIENT STARTING TEMP.	-40°F or -40°C				
NOM. OPEN CIRCUIT VOLTAGE	120				
INPUT VOLTAGE AT LAMP DROPOUT.....	98				
INPUT WATTS	84				
RECOMMENDED FUSE (Amps).....	4				
CORE and COIL					
Dimension (A)					
Dimension (B)					
Weight (lbs.)	5				
Lead Lengths					
CAPACITOR REQUIREMENT					
Microfarads					
Volts (min.)					
Fault Current Withstand (amps)					
60 Hz TEST PROCEDURES (Refer to Advance Test Procedure for HID Ballasts - Form 1270)					
High Potential Test (Volts)					
1 minute	2000				
2 seconds	2500				
Open Circuit Voltage Test (Volts)	108-132				
Short-Circuit Current Test (Amps)					
Secondary Current	2.10-3.10				
Input Current.....	1.30-2.00	-	-	-	-

Capacitor:

The capacitor is included as part of the potted assembly.

Wiring Diagram:



Postline Wiring Diagram

Ordering Information

Order Suffix	Description
011P	Thermally protected Ballast with kit
011P-XK	Thermally protected Ballast without kit

Ignitor:

IN CAN

The ignitor is included as part of the potted assembly.

Ballast to Lamp Distance
(BTL) = 10 feet
Temp Rating: 90°C

Data is based upon tests performed by Philips Lighting Electronic N.A. in a controlled environment and representative of relative performance. Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.

Philips Lighting Electronic N.A.

10275 West Higgins Road • Rosemont, IL 60018 • Tel:800-322-2086 Fax:888-432-1882
Customer Support/ Technical Service:800-372-3331 • OEM Support: 866-915-5886

09/08/97