

Linear

BoldPlay Suspended

3400 lm/4ft w/ 100% Down Kit*
3000/3500/4000K



Project: _____
Spec Type: _____
Catalog No: 7806LxEQJ
Qty _____
Line Notes: _____

Brilliant design and intuitive engineering fearlessly combine to deliver unprecedented performance. BoldPlay's striking contrast of effortless style and urban edginess makes a distinctive statement in any space. Available tunable white technology gives you the ability to vary color temperature and intensity, harmonizing lighting with your daily life.

Ordering guide

Product Type	Source	Color Temp *	Lumens *	Lower Optics	Upper Optics	Run Length	Wiring †	Voltage	Driver	Finish
7806	L		E	Q	J					
BoldPlay Direct/Indirect	L LED	A 4000K B 3500K C 3000K	A 6500 lm/4ft C 4600 lm/4ft E 3400 lm/4ft	Q MesoOptics Lens	N Lightguide D 55% Down Kit G 80% Down Kit J 100% Down Kit	04 4' 08 8' XX Total run length (4' increments)	7 1 cct Dimming E 2 cct A/B Dimming M 1 cct Dimming + EM Wiring N 1 cct Dimming + EM Batt. Pack	1 120V 2 277V 3 347V	E Philips Advance 0-10V (1% dim) S Philips Advance SR (5% dim)	W Standard White T Titanium Silver B Black C Custom

* Nominal values within a range. Down kits reduce output & efficacy. Consult photometry data for color temp, lumens & distribution of chosen configuration.


† Not all wiring types are available with all configurations. Consult Philips Ledalite for a complete list of available options.

Mounting Hardware

Mount Type
Consult separate mounting spec sheet for mount type options

Suspension Length
Distance from ceiling to top of luminaire in inches

Endcaps -



Integrated Controls Please indicate with check mark.

☐ Response Daylight Single Zone (DS)
☐ SpaceWise DT Occupancy & Daylight Sensor (SZ)

BoldPlay Suspended

3400 lm/4ft w/ 100% Down Kit*
3000/3500/4000K

Optical System

The optical system contains arrays of LEDs edge-lighting a low profile light-guide panel, using total internal reflection to homogenize the sources. The microstructured surface of the panel optimizes light extraction to create an efficacious direct/indirect distribution. Light is purified and controlled by MesoOptics film as it passes through a non-glare acrylic lens. Standard distribution is 75% up / 25% down for suspended and 65% up / 35% down for wall mount version.

Endcaps

Diecast aluminum endcaps.
Suspended: Available in sculpted (standard) or three flat (optional) versions: gloss black, gloss white & solid flat.
Wall: Three flat versions available: gloss black, gloss white & solid flat.

Finish

Standard finish is a textured matte powder coat in white, black or titanium silver. White sensors only.

Housing

Precision formed 18 gauge cold-rolled steel.

Weight

Maximum: Suspended 3.75lb/ft & Wall 3.0lb/ft.

Electrical

Factory pre-wired to section ends with quick-wire connectors.

Standard Driver

Philips Advance Xitanium 0-10V, 1-100%.
Philips Advance Xitanium SR, 5-100% (for SpaceWise DT). Class 2 rated output. Consult Philips Ledalite for other available drivers.

Standard Battery Pack

Philips Bodine, 90 min, 10W, Class 2 rated output, 1000lm nominal (@ 100lm/W; Flux = W x lm/W).

Lumen Maintenance

LEDs have been tested by the manufacturer in accordance with IESNA LM-80-08. At an ambient temperature of 25°C, the LED lumen maintenance expectation according to IES TM-21-11 is: L80 (12k) >72,000 hrs (Reported methodology).

Source Color

LEDs rated for color rendering CRI >80 and fixture to fixture color accuracy within 2 SDCM.

Controls

Suspended version available with the following integrated controls:
Response daylight sensor (for single zone).
SpaceWise DT occupancy & daylight sensor w/ advanced grouping & dwell time.
SpaceWise DT commissioning via Android phone and Philips Field App. Compatible dimming wireless wall switches are available. For more information, please refer to www.philips.com/spacewise

Mounting

Suspended: Tamper-resistant aircraft cable gripper provides unlimited vertical adjustment. Aircraft cable, crimp and cable gripper are independently tested to meet stringent safety requirements.
Wall: Fixture is mounted flush to wall using hidden wall brackets which attach to existing structure, variable within 2"-5" of end or joint.

Joints

Self-aligning joining system with hands-free pre-joining wire access.

Approvals

Certified to UL, CSA and IES standards.
Certain suspended versions without down kits are DesignLights Consortium® qualified. Please see the DLC QPL list for exact catalog numbers (www.designlights.org/QPL).

Warranty


Philips indoor professional luminaires 5 year LED warranty: www.philips.com/warranties.

Environment

Rated for dry or damp locations in operating ambient temperatures 0-40°C (32-104°F). Certain luminaire components may be adversely affected by contaminants. Damage caused by sulfur, chlorine, petroleum based solutions or other contaminants are not covered under warranty. Not suitable for natatorium environments.

Due to continuing product improvements, Philips Ledalite reserves the right to change the specifications without notice.

Dimensions - Cross Section





BoldPlay Suspended

3400 lm/4ft w/ 100% Down Kit*
3000/3500/4000K

Dimensions - Modules


Module length excludes end caps. Nominal mounting spacing for individually mounted modules.




Note: Refer to installation instructions for exact mount.

Optics and Styles


Lens view



End caps




Upper optics



BoldPlay Suspended

3400 lm/4ft w/ 100% Down Kit*
3000/3500/4000K

Photometry - 3500K



Candela Distribution

Vertical Angle	Horizontal Angle				Zonal Lumens
	0	22.5	45	67.5	90
0	877	877	877	877	877
5	880	880	884	888	889
15	896	903	940	974	983
25	900	917	989	1049	1071
35	830	840	886	918	922
45	627	619	611	600	594
55	408	400	388	385	385
65	242	239	240	243	248
75	100	101	102	104	105
85	19	20	22	22	22
90	0	0	0	0	0
95	1	1	1	1	1
105	1	2	3	3	1
115	2	2	3	2	2
125	2	3	2	2	2
135	2	2	2	3	2
145	2	2	2	3	2
155	2	2	2	2	3
165	2	2	2	1	2
175	1	1	1	1	1
180	1	1	1	1	1

Values per 4ft unit

Fixture photometry has been conducted in accordance with IESNA LM-79-08

IES files for this and other photometric options can be downloaded online at www.lightingproducts.philips.com

Coefficients of Utilization (%)

RCR	Ceiling					Wall					0				
	70	50	30	10	70	50	30	10	70	50	30	10	70	50	30
0	119	119	119	119	116	116	116	111	111	111	111	111	100	100	100
1	110	106	102	98	107	103	100	99	96	93	86	86	86	86	86
2	101	93	87	82	98	91	86	88	83	79	73	73	73	73	73
3	92	83	75	69	90	81	74	78	72	67	63	63	63	63	63
4	85	74	66	59	83	72	65	70	63	58	54	54	54	54	54
5	78	66	58	51	76	65	57	63	56	51	47	47	47	47	47
6	73	60	51	45	71	59	51	57	50	45	42	42	42	42	42
7	67	54	46	40	66	54	46	52	45	40	37	37	37	37	37
8	63	50	42	36	61	49	41	48	41	36	33	33	33	33	33
9	59	46	38	32	57	45	38	44	37	32	30	30	30	30	30
10	55	42	35	29	54	42	34	41	34	29	27	27	27	27	27

Avg. Luminance (cd/m2)

Vertical Angle	Horizontal Angle		
	0	45	90
55	6905	6570	6517
65	5561	5513	5705
75	3757	3836	3953
85	2092	2441	2441

Distribution

Hemisphere	0% Up / 100% Down
Glare Control	Meets RP-1-12 recommendations for VDT-Normal spaces
Spacing Along (0 °)	1.44
Spacing Across (90 °)	1.5

LED

lighting facts®

A Program of the U.S. DOE

Philips Ledalite

Light Output (Lumens)

2565

Watts

28.4

Lumens per Watt (Efficacy)

90.32

Color Accuracy

Color Rendering Index (CRI)

82

Light Color

Correlated Color Temperature (CCT)

3312 (Bright White)

Warm White

Bright White

Daylight

2700K

3000K

4500K

6500K

All results are according to IESNA LM-79-2008: Approved Method for the Electrical and Photometric Testing of Solid-State Lighting. The U.S. Department of Energy (DOE) verifies product test data and results.

Visit www.lightingfacts.com for the Label Reference Guide.

Registration Number: F46Z-WDD712 (10/28/2016)

Model Number: 7806LBEQJ

Type: Luminaire - Linear

BoldPlay Suspended

3400 lm/4ft w/ 100% Down Kit*
3000/3500/4000K

Optical Performance

Nominal CCT:	3000K	3500K	4000K
Flux (lm)	2457	2565	2639
Efficacy (lm/W)	86.2	90.3	93.3
Power (W)	28.5	28.4	28.3
CCT (K)	3045	3312	3931
CRI	84	82	83
R9	10	-1	5
x	0.4338	0.4167	0.3849
y	0.4031	0.3968	0.3837
Duv	0.0000	0.0000	0.0020

Electrical Performance - 3500K

Input Voltage	120V	277V	347V
Input Power	28.4W	28.4W	28.5W
Input Current	0.24A	0.11A	0.09A
Power Factor	0.994	0.962	0.953
Total Harm. Distortion	8.0%	11.6%	11.0%
Tested values . contact technical support for rated values. Off-state power zero unless certain controls are specified.			
With SpaceWise DT, standby power <0.5W (120V) or <0.8W (277V).			

