



Catalog No.	Lamp	
850WH	White	50W MR16 12V
850BK	Black	

Features

Lytespan Attachment Fitting: Molded polycarbonate. Integral color. Fitter twists onto track, lock on with push tab.

Push Tab: Molded polycarbonate. Detaches unit.

Polarity Keyway.

Converter Housing: Molded polycarbonate. Integral color.

Converter: Low voltage 120V/12V electronic. 18AWG, SEW-1. Use a conventional dimmers. Note: electronic converters may become audible when used with wall dimmers.

Pivot Mounting: Permanently tensioned. Adjust horizontally with 350° stop.

Yoke: 0.075" (1.90mm) steel.

Pivot Mounting: Tensioned with integral spring washer. Adjusts vertically up to 180°.

Lamp Shield: 0.020" (0.51mm) steel.

Lampholder: Miniature bi-pin, GX5, 3 base, nickel contacts. 18AWG, AWM.

Housing: 0.016" (0.41mm) steel.

Protective Glass: Clear borosilicate, filters out U.V. radiation and lamp rupture as required by CSA.

Protective Glass: Clear borosilicate, filters out U.V. radiation and lamp rupture as required by CSA.

Finish

All painted finishes are baked powder or enamel.

Marking

CSA Cerified, suitable for dry locations only.

Mounting

All Basic (single circuit) track systems only.

Accessory

AF2 / ADF2 Series ; 2" dia. Filters and Lenses ; Max. of one accessory.

7472 ; Hex cell louver

Job Information	Type:
Job Name:	
Cat. No.:	
Lamp(s):	
Notes:	