


Brilliant design and intuitive engineering fearlessly combine to deliver unprecedented performance. BoldPlay's striking contrast of effortless style and urban edginess makes a distinctive statement in any space. Available tunable white technology gives you the ability to vary color temperature and intensity, harmonizing lighting with your daily life.

Ordering guide



Mount Type Consult separate mounting spec sheet for mount type options Endcaps Sculpted Gloss white flat Solid flat Suspension Length Distance from ceiling to top of luminaire in inches Integrated Controls Please indicate with check mark. No Options Available

^{*} Nominal values within a range. Down kits reduce output & efficacy. Consult photometry data for exact color temp, lumens & distribution.

[†] Not all wiring types are available with all configurations. Consult Philips Ledalite for a complete list of available options.

BoldPlay

4600 lm/4ft 75% Up Tunable White, 2700-6500K

Housing

Precision formed 18 gauge cold-rolled steel.

Weight

Maximum: Suspended 3.75lb/ft & Wall 3.0lb/ft

Optical System

The optical system contains arrays of LEDs edge lighting a low profile light-guide panel, using total internal reflection to homogenize the sources. The microstructured surface of the panel optimizes light extraction to create an efficacious direct/indirect distribution. Light is purified and controlled by MesoOptics film as it passes through a non-glare acrylic lens. Standard distribution is 70% up / 30% down.

Endcaps

Diecast aluminum endcaps; available in sculpted (standard) or flat (optional). Three flat versions: gloss black, gloss white & solid flat are available.

Finish

High quality powder coated, available in matte white, black or titanium silver. Other custom colors available on request.

Electrical

Factory pre-wired to section ends with quick-wire connectors.

Lumen Maintenance

Lumen maintenance of the LEDs has been tested by the manufacturer in accordance with IESNA LM-80-08. At an ambient temperature of 25°C, the LED lumen maintenance expectation is L80(12K)>72,000h according to IES TM-21-11 Addendum A Reported methodology.

Housing

Precision formed 18 gauge cold-rolled steel.

Weight

Maximum: Suspended 3.75lb/ft

Mounting

Mounting

Tamper-resistant aircraft cable gripper provides infinite vertical adjustment capability. Aircraft cable, crimp and cable gripper are independently tested to meet stringent safety requirements.

Joints

Self-aligning joining system with hands-free pre-joining wire access.

Approvals

Certified to UL, CSA and IES standards.

Warranty

Philips indoor professional luminaires 5 year LED warranty: http://www.philips.com/warranties.

Environment

Rated for dry or damp locations in operating ambient temperatures $0-40^{\circ}\text{C}$ (32- 104°F). Certain luminaire components may be adversely affected by contaminants. Damage caused by sulfur, chlorine, petroleum based solutions or other contaminants are not covered under warranty.

Dimming


Color accuracy held to 5% at 2700K and 6500K and 10% at 4000K.

Controls

Luminaires are not sold individually and are only compatible with load controllers, sensors, user interfaces and front end software from Philips. Philips controls platform allows for more flexibility with customized lighting scenes and behaviors as well as scalability of the tunable white solution into a more extensive lighting network management system. To learn more about the Philips controls solution please visit our tunable white page or http://www.lightingproducts.philips.com/our-brands/philips-controls/dynalite.html

Due to continuing product improvements, Philips Ledalite reserves the right to change the specifications without notice.

Dimensions - Cross Section



BoldPlay Suspended LED Tunable White

4600 lm/4ft 75% Up Tunable White, 2700-6500K

Tunable White, 2700-6500K			
Dimensions - Modules			
Module length excludes end caps. Nomina	al mounting spacing for individually mou	nted modules.	
4' (1219.2mm)			
4 ft.			
L	Q! (242Q Qaaya)		
	8' (2438.8mm) —		
8 ft.			
		Note	: Refer to installation instructions for exact moun
Optics and Styles			
Lens view			
←	8' 3/8"		→
Suspended (without endcaps)			
End caps	Uį	pper optics	

G 80% Down Kit

J 100% Down Kit


Sculpted

Flat

BoldPlay Suspended LED Tunable White

4600 lm/4ft 75% Up Tunable White, 2700-6500K

Photometry - 2700K



77% Up / 23% Down

Candela Distribution

Vertical	Horizontal Angle				Zonal	
Angle	0	22.5	45	67.5	90	Lumens
0	313	313	313	313	313	0
5	317	319	326	329	341	32
15	337	348	384	410	425	109
25	355	382	440	504	523	202
35	338	368	402	471	460	252
45	254	274	269	299	281	215
55	170	172	163	175	173	154
65	96	95	91	94	97	94
75	38	32	29	23	30	33
85	5	0	0	0	0	3
90	0	1	0	2	0	0
95	154	164	275	373	449	292
105	377	425	669	949	1172	732
115	492	562	796	1106	1263	818
125	509	573	730	951	1032	677
135	484	534	609	731	764	486
145	465	499	537	583	598	340
155	457	481	502	522	526	232
165	451	465	477	485	488	135
175	446	450	452	458	456	44
180	444	444	444	444	444	0

Values per 4ft unit

Fixture photometry has been conducted in accordance with IESNA LM-79-08

IES files for this and other photometric options can be downloaded online at www.lightingproducts.philips.com

Coefficients of Utilization (%)

1 92 88 84 81 82 78 75 60 58 56 2 84 77 71 67 74 69 64 53 50 47 3 77 66 61 56 68 60 55 47 43 40 64 53 66 55 64 55 64 55 64 55 64 55 64 55 64 55 64 55 64 55 64 55 64 55 64 55 64 55 64 55 64 55 64 64 55 64 65 55 64 81 37 32 29 55 64 55 64 64 55 64 64 55 55 64 36 33 29 25 56 66 66 66 66 67 67 68	0
1 92 88 84 81 82 78 75 60 58 56 2 84 77 71 67 74 69 64 53 50 47 3 77 66 61 56 68 60 55 47 43 40 64 53 66 55 64 55 64 55 64 55 64 55 64 55 64 55 64 55 64 55 64 55 64 55 64 55 64 55 64 55 64 55 64 64 55 64 65 55 64 81 37 32 29 55 64 55 64 64 55 64 64 55 55 64 36 33 29 25 56 66 66 66 66 67 67 68	
2 84 77 71 67 74 69 64 53 50 47 3 77 68 61 56 68 60 55 47 43 40 4 70 60 53 47 62 54 47 41 37 34 5 64 53 46 40 57 48 41 37 32 29 6 6 59 48 40 35 52 43 36 33 29 25	23
3	20
4 70 60 53 47 62 54 47 41 37 34 5 64 53 46 40 57 48 41 37 32 29 6 59 48 40 35 52 43 36 33 29 25 5	17
5 64 53 46 40 57 48 41 37 32 29 5 6 59 48 40 35 52 43 36 33 29 25	15
6 59 48 40 35 52 43 36 33 29 25	13
	11
7 54 43 35 30 48 38 32 30 25 22	10
	9
	8
9 47 35 28 23 41 32 25 25 20 17	7
10 43 32 25 21 39 29 23 23 18 15	6

Avg. Luminance (cd/m2)

Vertical	Horizontal Angle			
Angle	0	45	90	
55	2887	2776	2952	
65	2206	2100	2243	
75	1418	1094	1128	
85	527	0	0	

Distribution


Hemisphere	77% Up / 23% Down
Peak/Zenith	2.87
Peak Output	1273 cd
Glare Control	Meets RP-1-12 recommendations for VDT-Critical spaces

BoldPlay Suspended LED Tunable White

4600 lm/4ft 75% Up Tunable White, 2700-6500K

Optical Performance

Nominal CCT:	3500K	4000K	5000K	6500K	2700K	3000K
Flux (lm)	5007	5123	4993	4916	4850	4972
Efficacy (lm/W)	99.5	101.2	100.1	100.1	97.4	94.9
Power (W)	50.3	50.6	49.9	49.1	49.8	52.4
CCT (K)	3329	3809	4670	6188	2664	2877
CRI	86	87	87	84	82	84
R9	22	27	27	12	7	13
x	0.4094	0.3849	0.3539	0.3184	0.4612	0.4414
у	0.3812	0.3681	0.3514	0.3321	0.4084	0.3980
Duv	-0.0051	-0.0054	-0.0036	0.0020	-0.0009	-0.0030



Electrical Performance - 2700K

Input Voltage 120V 277V					
Input Power	49.8W	49.2W			
Input Current	0.42A	0.19A			
Power Factor 0.994 0.919					
Total Harm. Distortion 7.4% 12.1%					
Tested values – contact technical support for rated values.					

Non Commissioned State

Input Voltage	120V	277V
Input Power	97.8	96.4
Input Current	0.82	0.36

© 2016 Philips Lighting Holding B.V. Il rights reserved. Philips reserves the right to make changes in specifications and/or to discontinue any product at any time without notice or obligation and will not be liable for any consequences resulting from the use of this publication.

www.philips.com/luminaires



Philips Lighting, North America Corporation 200 Franklin Square Drive, Somerset, NJ 08873 Tel. 855-486-2216

Philips Lighting Canada Ltd., 281 Hillmount Rd, Markham, ON, Canada L6C 2S3 Tel. 800-668-9008