


PHILIPS ADVANCE

High Pressure Sodium Lamp Ballast

Catalog Number 71A8371
For 310W S67
60 Hz CWA
Status: Active

DIMENSIONS AND DATA

4 1/4 X 4 3/4 CORE - 2 COIL UNIT




	120	208	240	277
INPUT VOLTS				
CIRCUIT TYPE	CWA			
POWER FACTOR (min)	90%			
REGULATION	±10%			
Line Volts	WITHIN TRAPEZOID			
Lamp Watts				
LINE CURRENT (Amps)				
Operating.....	3.37	1.94	1.68	1.45
Open Circuit.....	1.80	1.00	0.90	0.80
Starting.....	1.70	0.89	0.85	0.75
UL TEMPERATURE RATINGS				
Insulation Class	H(180°C)			
Coil Temperature Code	1029			
MIN. AMBIENT STARTING TEMP.	-40°F or -40°C			
NOM. OPEN CIRCUIT VOLTAGE	175			
INPUT VOLTAGE AT LAMP DROPOUT.....	90	156	180	208
INPUT WATTS	365			
RECOMMENDED FUSE (Amps).....	8	5	5	5
CORE and COIL				
Dimension (A)	2.15			
Dimension (B)	4.10			
Weight (lbs.)	13.5			
Lead Lengths	12"			
CAPACITOR REQUIREMENT				
Microfarads	45.0			
Volts (min.)	280			
Fault Current Withstand (amps)				
60 Hz TEST PROCEDURES (Refer to Advance Test Procedure for HID Ballasts - Form 1270)				
High Potential Test (Volts)				
1 minute	2000			
2 seconds	2500			
Open Circuit Voltage Test (Volts)	155-195			
Short-Circuit Current Test (Amps)				
Secondary Current	4.40-5.40			
Input Current.....	1.40-2.20	0.80-1.25	0.70-1.10	0.60-0.95

Capacitor: 7C450P30RA



Capacitance: 45
 Dia/Oval Dim: 1.85
 Height: 4.7
 Temp Rating: 105°C

Wiring Diagram:



Ordering Information

Order Suffix

Description

Ignitor: LI501-H4



Ballast to Lamp Distance (BTL) = 2 feet
 Temp Rating: 105°C

Data is based upon tests performed by Philips Lighting Electronic N.A. in a controlled environment and representative of relative performance. Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.

Philips Lighting Electronic N.A.

10275 West Higgins Road · Rosemont, IL 60018 · Tel:800-322-2086 Fax:888-432-1882
 Customer Support/ Technical Service:800-372-3331 · OEM Support: 866-915-5886

06/25/13