




PHILIPS

TrueLine


RC530B EL




			kg	
			VPC	PCV
Recessed	VPC	W8L150	1497	1450
Recessed	PCV	W8L145	1472	1450
Recessed Line	VPC/PCV	W8L145	1448	4.2



Optional: RC530Z EP SET WH



Inrush current




$I_{max}(A)$	19
$T_{ref}(\mu s)$	280

Condition:
Input voltage 220V


MCB	Luminaire's Max.
B-10A	15
B-13A	19
B-16A	24
B-20A	30
B-25A	37
C-10A	24
C-13A	32
C-16A	40
C-20A	49
C-25A	62




Recessed




1





Wieland







2




3




PC V



4



5





Recessed Line

