




Ordering Information

Catalog No.	Finish	Mounting	Lamps
22SS8WH 22SS8BK 22SS8AL	Matte White Matte Black Metallic Aluminum	All Lytespan Track Systems. Does not mount on ProSpec Track.	PAR38 Maximum 150W

Features

- Track Attachment Fitting:** Locking lever for mechanical/electrical connection
- Brass Contact:** Extends for connection to second circuit (Advent Lytespan track only)
- Horizontal Pivot:** Wireless stem profile with 365° horizontal rotation
- Vertical Pivot:** 0-90° vertical adjustment
- Socket:** Porcelain socket, medium base, nickel-plated screw shell
- Housing:** Die cast aluminum
- Accessory Cartridge:** Hinged and captive; retaining ring included

Finish

All Painted finishes are baked enamel.

Dimming

Fixture may be used on a track with a dimmer.
Consult dimmer manufacturer for correct dimmer selection.

Accessories

Accessory Holder: Integral
Accessories: Accepts two total
(1 lens + 1 louver or 2 lenses)
Lens: AF4, ADF4. Not compatible with AF4IR
Louver: AL4HC

Labels

UL, cUL

Job Information

Type:

Job Name:

Cat. No.:

Lamp(s):

Notes:



AIMING ANGLE:

L Beam length
W Beam Width
C Distance to center beam
D Distance
A Aiming Angle
FC Footcandles

L and **W** are the outer points where the candle power drops to 50% of the maximum. **FC** are the initial footcandles at the center of the beam.

Lamp data shown is typical. Consult lamp manufacturers for availability and performance. CBCP= Center Beam Candle Power.

LAMP

	Beam Spread (To 50% CBCP)	CBCP	Rated Life (hrs.)	D	FC	L	W	D	C	FC	L	W	D	C	FC	L	W	D	C	FC	L	W
50W PAR20 SP	10°	4,600	2,500	6'	128	1.0'	1.0'	8'	4.6'	47	1.9'	1.6'	2'	3.5'	144	1.4'	0.7'	4'	4.0'	102	1.4'	1.0'
				8'	72	1.4'	1.4'	12'	6.9'	21	2.8'	2.4'	5'	5.2'	64	2.1'	1.0'	5'	5.0'	65	1.8'	1.2'
				10'	46	1.7'	1.7'	14'	8.1'	15	3.3'	2.8'	6'	6.9'	36	2.9'	1.4'	6'	6.0'	45	2.1'	1.5'
				12'	32	2.1'	2.1'	16'	9.2'	12	3.7'	3.2'	7'	7.0'	23	3.6'	1.7'	7'	7.0'	33	2.5'	1.7'
50W PAR20 NFL	25°	1,500	2,500	4'	116	1.9'	1.9'	3'	1.7'	134	2.0'	1.7'	1'	1.7'	231	2.3'	1.0'	3'	3.0'	73	3.1'	2.0'
				6'	51	2.9'	2.9'	5'	2.9'	48	3.3'	2.8'	2'	3.5'	58	4.6'	1.9'	4'	4.0'	41	4.1'	2.7'
				8'	29	3.8'	3.8'	7'	4.0'	25	4.6'	3.9'	3'	5.2'	26	7.0'	2.9'	5'	5.0'	26	5.1'	3.4'
				10'	19	4.8'	4.8'	9'	5.2'	15	5.9'	5.0'	4'	6.9'	14	9.3'	3.8'	6'	6.0'	18	6.1'	4.1'
50W PAR30 FL	35°	1,400	3,000	6'	39	3.8'	3.8'	6'	3.5'	25	5.2'	4.4'	2'	3.5'	44	7.2'	2.5'	3'	3.0'	124	2.8'	1.8'
				8'	29	4.4'	4.4'	7'	4.0'	19	6.1'	5.1'	3'	5.2'	19	10.8'	3.8'	4'	4.0'	55	4.2'	2.7'
				9'	22	5.0'	5.0'	8'	4.6'	14	7.0'	5.8'	4'	6.9'	11	14.4'	5.0'	4'	4.0'	31	5.6'	3.6'
				9'	17	5.7'	5.7'	9'	5.2'	11	7.8'	6.6'	5'	8.7'	7	18.0'	6.3'	5'	5.0'	20	7.0'	4.5'
60W PAR16 NSP	10°	5,000	2,000	6'	139	1.0'	1.0'	5'	2.9'	130	1.2'	1.0'	2'	3.5'	156	1.4'	0.7'	3'	3.0'	196	1.1'	0.7'
				8'	78	1.4'	1.4'	7'	4.0'	66	1.6'	1.4'	3'	5.2'	69	2.1'	1.0'	5'	5.0'	71	1.6'	1.2'
				10'	50	1.7'	1.7'	9'	5.2'	40	2.1'	1.8'	4'	6.9'	39	2.9'	1.4'	7'	7.0'	36	2.5'	1.7'
				12'	35	2.1'	2.1'	11'	6.4'	27	2.6'	2.2'	5'	8.7'	25	3.6'	1.7'	9'	9.0'	22	3.2'	2.2'
60W PAR16 NFL	30°	1,300	2,000	3'	144	1.6'	1.6'	3'	1.7'	94	2.2'	1.9'	1'	1.7'	163	2.7'	1.1'	2'	2.0'	115	2.3'	1.5'
				5'	52	2.7'	2.7'	5'	2.9'	34	3.7'	3.1'	2'	3.5'	41	5.5'	2.1'	3'	3.0'	51	3.5'	2.3'
				7'	27	3.8'	3.8'	7'	4.0'	17	5.1'	4.3'	3'	5.2'	18	8.2'	3.2'	4'	4.0'	29	4.6'	3.0'
				9'	16	4.8'	4.8'	9'	5.2'	10	6.6'	5.6'	4'	6.9'	10	10.9'	4.3'	5'	5.0'	18	5.8'	3.8'
75W PAR30 NSP	10°	13,000	3,000	8'	219	1.3'	1.3'	7'	4.0'	186	1.5'	1.3'	3'	5.2'	194	1.9'	0.9'	5'	5.0'	196	1.6'	1.1'
				12'	97	1.9'	1.9'	10'	5.8'	91	2.1'	1.8'	4'	6.9'	109	2.6'	1.3'	7'	7.0'	101	2.2'	1.6'
				16'	55	2.5'	2.5'	13'	7.5'	54	2.7'	2.4'	5'	8.7'	70	3.2'	1.6'	9'	9.0'	61	2.9'	2.0'
				20'	35	3.1'	3.1'	16'	9.2'	36	3.4'	2.9'	6'	10.4'	49	3.6'	1.9'	11'	11.0'	41	3.5'	2.4'
75W PAR30 NFL	25°	3,800	3,000	6'	106	2.7'	2.7'	6'	3.5'	69	3.6'	3.1'	2'	3.5'	119	4.2'	1.8'	4'	4.0'	84	3.7'	2.5'
				8'	59	3.5'	3.5'	8'	4.6'	39	4.8'	4.1'	3'	5.2'	53	6.2'	2.7'	5'	5.0'	54	4.7'	3.1'
				10'	38	4.4'	4.4'	10'	5.8'	25	6.0'	5.1'	4'	6.9'	30	8.3'	3.5'	6'	6.0'	37	5.6'	3.8'
				12'	26	5.3'	5.3'	12'	6.9'	17	7.2'	6.1'	5'	8.7'	19	10.4'	4.4'	7'	7.0'	27	6.5'	4.4'
90W PAR38 NSP	9°	19,500	2,500	10'	195	1.6'	1.6'	8'	4.6'	198	1.7'	1.5'	4'	6.9'	152	2.6'	1.3'	6'	6.0'	192	1.9'	1.3'
				15'	87	2.4'	2.4'	12'	6.9'	88	2.5'	2.2'	6'	10.4'	60	3.8'	1.9'	9'	9.0'	85	2.9'	2.0'
				20'	49	2.4'	2.4'	16'	9.2'	49	3.4'	2.9'	8'	13.9'	38	5.1'	2.5'	12'	12.0'	48	3.8'	2.7'
				25'	31	3.9'	3.9'	20'	11.5'	32	4.2'	3.6'	10'	17.3'	24	6.4'	3.1'	15'	15.0'	31	4.8'	3.3'
90W PAR38 SP	12°	14,500	2,500	8'	227	1.7'	1.7'	7'	4.0'	192	2.0'	1.7'	3'	5.2'	201	2.6'	1.3'	5'	5.0'	205	2.1'	1.5'
				12'	101	2.5'	2.5'	10'	5.8'	94	2.8'	2.4'	4'	6.9'	113	3.5'	1.7'	7'	7.0'	105	3.0'	2.1'
				16'	57	3.4'	3.4'	13'	7.5'	56	3.7'	3.2'	5'	8.7'	73	4.3'	2.1'	9'	9.0'	63	3.8'	2.7'
				20'	36	4.2'	4.2'	16'	9.2'	37	4.5'	3.9'	6'	10.4'	50	5.2'	2.5'	11'	11.0'	42	4.7'	3.3'
90W PAR38 NFL	28°	4,500	2,500	6'	125	3.0'	3.0'	5'	2.9'	117	3.4'	2.9'	2'	3.5'	141	4.9'	2.0'	3'	3.0'	177	3.2'	2.1'
				8'	70	4.0'	4.0'	7'	4.0'	60	4.8'	4.0'	3'	5.2'	63	7.4'	3.0'	5'	5.0'	64	5.3'	3.5'
				10'	45	5.0'	5.0'	9'	5.2'	36	6.1'	5.2'	4'	6.9'	35	9.8'	4.0'	7'	7.0'	32	7.4'	4.9'
				12'	31	6.0'	6.0'	11'	6.4'	24	7.5'	6.3'	5'	8.7'	23	12.3'	5.0'	9'	9.0'	20	9.6'	6.3'
90W PAR38 WFL	55°	2,250	2,500	6'	63	6.2'	6.2'	6'	3.5'	41	9.2'	7.2'	2'	3.5'	70	44.5'	4.2'	3'	3.0'	199	5.7'	2.9'
				7'	46	7.3'	7.3'	7'	4.0'	30	10.7'	8.4'	3'	5.2'	31	66.8'	6.2'	4'	4.0'	88	8.6'	4.4'
				8'	35	8.3'	8.3'	8'	4.6'	23	12.2'	9.6'	4'	6.9'	18	89.1'	8.3'	5'	5.0'	50	11.4'	5.9'
				9'	28	9.4'	9.4'	9'	5.2'	18	13.7'	10.8'	5'	8.7'	11	111.3'	10.4'	5'	5.0'	32	14.3'	7.4'
120W PAR38 NSP	10°	25,000	3,000	10'	250	1.7'	1.7'	8'	4.6'	254	1.9'	1.6'	4'	6.9'	195	2.9'	1.4'	6'	6.0'	246	2.1'	1.5'
				15'	111	2.6'	2.6'	12'	6.9'	113	2.8'	2.4'	6'	10.4'	87	4.3'	2.1'	9'	9.0'	109	3.2'	2.2'
				20'	63	3.5'	3.5'	16'	9.2'	63	3.7'	3.2'	8'	13.9'	49	5.7'	2.8'	12'	12.0'	61	4.2'	3.0'
				25'	40	4.4'	4.4'	20'	11.5'	41	4.7'	4.0'	10'	17.3'	31	7.2'	3.5'	15'	15.0'	39	5.3'	3.7'
120W PAR38 FL	30°	4,600	3,000	6'	139	3.2'	3.2'	5'	2.9'	130	3.7'	3.1'	2'	3.5'	156	5.5'	2.1'	3'	3.0'	196	3.5'	2.3'
				8'	78	4.3'	4.3'	7'	4.0'	66	5.1'	4.3'	3'	5.2'	69	6.2'	3.2'	4'	4.0'	71	5.8'	3.8'
				10'	50	5.4'	5.4'	9'	5.2'	40	6.6'	5.6'	4'	6.9'	39	10.9'	4.3'	5'	5.0'	36	8.1'	5.3'
				12'	35	6.4'	6.4'	11'	6.4'	27	8.1'	6.8'	5'	8.7'	25	13.7'	5.4'	6'	6.0'	22	10.4'	6.8'
120W PAR38 WFL	55°	2,000	3,000	4'	125	3.7'	3.7'	3'	1.7'	144	4.0'	3.2'	1'	1.7'	250	10.7'	1.9'	4'	4.0'	79	7.2'	4.0'
				6'	56	5.6'	5.6'	5'	2.9'	52	6.7'	5.4'	4'	3.5'	63	21.5'	3.7'	5'	5.0'	44	9.5'	5.3'
				8'	31	7.5'	7.5'	7'	4.0'	27	9.4'	7.5'	3'	5.2'	28	32.2'	5.6'	5'	5.0'	28	11.9'	6.6'
				10'	20	9.3'	9.3'	9'	5.2'	16	12.1'	9.7'	4'	6.9'	16	42.9'	7.5'	6'	6.0'	20	14.3'	7.9'
250W PAR38 SP	10°	46,500	4,500	12'	323	2.1'	2.1'	6'	10.4'	161	4.3'	2.1'	3'	5.2'	125	8.2'	3.2'	6'	6.0'	457	2.1'	1.5'
				16'	182	2.8'	2.8'	8'	13.9'	91	5.7'	2.8'	4'	6.9'	70	10.9'	4.3'	8'	8.0'	257	2.8'	2.0'
				20'	116	3.5'	3.5'	10'	17.3'	58	7.2'	3.5'	10'	17.3'	58	7.2'	3.5'	10'	10.0'	164	3.5'	2.5'
				24'	81	4.2'	4.2'	12'	20.8'	40	8.6'	4.2'	12'	20.8'	40	8.6'	4.2'	12'	12.0'	114	4.2'	3.0'
250W PAR38 FL	30°	9,000	4,500	8'	141	4.3'	4.3'	8'	4.6'	91	5.9'	5.0'	3'	5.2'	125	8.2'	3.2'	4'	4.0'	199	4.6'	3.0'
				10'	90	5.4'	5.4'	10'	5.8'	58	7.3'	6.2'	4'	6.9'	70	10.9'	4.3'	5'	5.0'	127	5.8'	3.8'
				12'	63	6.4'	6.4'	12'	6.9'	41	8.8'	7.4'	5'	8.7'	45	13.7'	5.4'	6'	6.0'	88	6.9'	4.5'
				14'	46	7.5'	7.5'	14'	8.1'	30	10.2'	8.7'	6'	10.4'	31	16.4'	6.4'	7'	7.0'	65	8.1'	5.3'

Job Information

Type:

Lightolier a Genlyte company

631 Airport Road, Fall River, MA 02720 • (508) 679-8131 • Fax (508) 674-4710

We reserve the right to change details of design, materials and finish.

© 2005 Genlyte Group LLC • B0205

www.lightolier.com

LIGHTOLIER®