






Project:	
Spec Type:	
Catalog No:	4114SxxxL8xD
Qty	
Line Notes:	

Specifically designed to blend high performance LED technology with versatile options to suit any area, VersaForm allows you to enjoy the latest LED energy efficiencies in concert with your unique style, and as your needs evolve, it's simple to change or upgrade with our unique detachable light engine.

## **Ordering guide**



Upgrades & Accessories Please indicate with check mark.



<sup>\*</sup> Nominal values within a range. Consult photometry data for color temp, lumens & distribution of chosen configuration. † Not all wiring types are available with all configurations. Consult Philips Ledalite for a complete list of available options.

## **VersaForm**

1'x4', 4000 lm 3000/3500/4000K

### **Optical System**

The optical frame assembly consists of integrated LED arrays edge lighting a light guide panel in order to deliver uniform controlled light through a lower lens. The optical frame ends are constructed from die-formed cold-rolled steel, assembled together with extruded aluminum profiles in a sturdy frame. The frame is hinged (side marked) to allow easy access to the inside of the fixture. Maintenance can be performed from below the ceiling.

#### **Finish**

Housing and frame painted, high quality, powder coated matte white only.

### Housing

Die-formed, post painted, 22 gauge cold-rolled steel. Wire entrance with additional knock-out available on top side for electrical connections.

#### Weight

Maximum 28lbs (2x4); 21lbs (1x4); 15lbs (2x2).

#### Electrical

Factory pre-wired with driver safety disconnect.

#### Mounting

Recessed: Fixtures can be fastened directly to the T-bar grid and/or tied-off to the building structure. Optional drywall kit trim mount can be fastened to a wood frame or with hangar wire. Continous row mounting not available with drywall kit trim mounts.

**Surface:** Fixtures can be mounted over recessed junction box and side entry also available.

#### Standard Driver

Philips Advance Xitanium 0-10V, 1-100%, Class 2 rated output. Consult Philips Ledalite for other available drivers.

#### **Standard Battery Pack**

Philips Bodine, 90 min, 10W, Class 2 rated output, Emergency lumen output = 10W x luminaire efficacy x 1.1. Typical output: 1100lm.

#### **Lumen Maintenance**

LEDs have been tested by the manufacturer in accordance with IESNA LM-80-08. At an ambient temperature of  $25^{\circ}$ C, the LED lumen maintenance expectation according to IES TM-21-11 is: L90 (9k) >54,000 hrs (**Reported** methodology). L80 (9k) 145,000 hrs (**Projected** methodology).

#### Source Color

LEDs rated for color rendering CRI >80, R9 >0 and fixture to fixture color accuracy within 2 SDCM.

#### Controls

Available with the following integrated controls: Response daylight sensor (for single zone).

## Wiring

Recessed: Optional flex whips are supplied in 6' lengths. Surface: Standard wiring configurations available.

#### **Approvals**

Certified to UL, CSA, and IES standards. City of Chicago Approved CCEA (housing option C). Certain versions without battery packs are DesignLights Consortium® qualified. Please see the DLC QPL list for exact catalog numbers (www.designlights.org/QPL).

### Warranty

Five-year luminaire limited warranty including LED boards and driver.

USA: http://www.usa.lighting.philips.com/support/support/warranty

Canada: http://www.lighting.philips.ca/support/support/warrantv

#### **Environment**


Rated for dry & damp locations in operating ambient temperatures of  $0-25^{\circ}\mathrm{C}$  (32–77°F). Many luminaire components, such as reflectors, refractors, lenses, and LEDs are made from various types of plastics which can be adversely affected by airborne contaminants. If sulfur based chemicals, petroleum based products, cleaning solutions, or other contaminants are expected in the intended area of use, consult factory for compatibility. Damage caused by sulfur, chlorine, petroleum based solution or other contaminants are not covered under warranty.

Due to continuing product improvements, Philips Ledalite reserves the right to change the specifications without notice.

## **Options and Details**

## Mounting


## **Cross Section**




# **VersaForm**

1'x4', 4000 lm 3000/3500/4000K

## Photometry - 3500K



0% Up / 100% Down



## Candela Distribution

Vertical		Ho	rizontal /	Angle		Zonal
Angle	0	22.5	45	67.5	90	Lumens
0	980	980	980	980	980	0
5	979	978	984	987	985	94
15	972	978	999	1019	1025	284
25	947	962	1016	1070	1091	470
35	884	911	998	1091	1129	626
45	768	801	904	1015	1065	699
55	602	631	719	817	863	646
65	407	426	482	545	577	481
75	213	220	245	274	287	263
85	56	54	57	57	53	66
90	0	0	0	0	0	0
95	0	0	0	0	0	0
105	0	0	0	0	0	0
115	0	0	0	0	0	0
125	0	0	0	0	0	0
135	0	0	0	0	0	0
145	0	0	0	0	0	0
155	0	0	0	0	0	0
165	0	0	0	0	0	0
175	0	0	0	0	0	0
180	0	0	0	0	0	0

Fixture photometry has been conducted in accordance with IESNA LM-79-08

IES files for this and other photometric options can be downloaded online at www.lightingproducts.philips.com

## Coefficients of Utilization (%)

RCR	Ceiling:		8	0			70			50		0
KCK	Wall:	70	50	30	10	70	50	30	50	30	10	0
0		119	119	119	119	116	116	116	111	111	111	100
1		108	103	99	95	106	101	97	97	94	91	83
2		98	90	83	77	95	88	81	84	79	74	68
3		89	78	70	63	87	77	69	73	67	61	57
4		81	69	60	53	79	67	59	65	57	52	48
5		74	61	52	45	72	60	51	58	50	44	41
6		68	55	45	39	66	54	45	52	44	38	35
7		63	49	40	34	61	48	40	47	39	33	31
8		59	45	36	30	57	44	36	43	35	30	27
9		55	41	32	27	53	40	32	39	32	26	24
10		51	38	29	24	50	37	29	36	29	24	22

## Avg. Luminance (cd/m2)

Vertical	Horizontal Angle				
Angle	0	45	90		
55	3570	4268	5120		
65	3280	3878	4646		
75	2800	3223	3777		
85	2175	2224	2079		

## **Distribution Summary**

Hemisphere	0% Up / 100% Down
Spacing Along (0°)	1.39
Spacing Across (90 °)	1.7

# **VersaForm**

1'x4', 4000 lm 3000/3500/4000K

## **Optical Performance**

Flux (lm)	3896	3629	3536
Efficacy (lm/W)	111.0	103.7	101.0
Power (W)	35.1	35.0	35.0
сст (к)	3876	3328	2973
CRI	83	82	81
R9	12	6	4
x	0.3878	0.4179	0.4412
у	0.3861	0.4018	0.4096
Duv	0.0020	0.0020	0.0020

### **Electrical Performance - 3500K**

Input Voltage	120V	277V	347V
Input Power	35.0VV	34.9W	34.4W
Input Current	0.30A	0.14A	0.10A
Power Factor	0.986	0.897	0.965
Total Harm. Distortion	14.7%	18.5%	9.0%

Tested values . contact technical support for rated values. Off-state power zero unless certain controls are specified.  $\frac{1}{2} \frac{1}{2} \frac{1$ 

