


Track

Alcyon LED

Recessed Vertical Cylinder,
LLAVRM, 10W/900lm,
15W/1300lm, 21W/2000lm



Project: _____
Location: _____
Cat.No: _____
Type: _____
Lamps: _____ Qty: _____
Notes: _____

Alcyon LED Vertical Cylinders are ideal for display, accent and task lighting and offer higher efficiency than incandescent or halogen sources leading to energy savings with no ultraviolet or infrared radiation. Alcyon provides concentrated light which dramatically draws interest to objects and elements in a space.

Frame-in kit

example: LLAVRM11H2120

Series	Lumens	Heads	Voltage
LLAVRM	☐	☐	☐
LLAVRM Alcyon LED Recessed Vertical Cylinder	11 900 /1300lm 12 2000lm	H1 1 head H2 2 head H3 3 head H4 4 head	120 120V 277 277V

Fixture

example: LLAVRMWH1130H2

Series	Finish	Lumens	CCT	CCT	Heads
LLAVRM	☐	☐	☐	☐	☐
LLAVRM Alcyon LED Recessed Vertical Cylinder	WH White BK Black	01 900lm 11 1300lm 12 2000lm	– 80CRI	27 2700K 30 3000K 40 4000K	H1 1 head H2 2 head H3 3 head H4 4 head

Reflector

example: LLAV12RNS


Series	Lumens	Reflector
LLAV	☐	☐
LLAV Alcyon LED Vertical Cylinder	11 900 /1300lm 12 2000lm	RNS Narrow Spot RS Spot RNF Narrow flood RF Flood

Accessories

example: LLA11SNBK

Series	Finish
☐	☐
Accessory holder with spring LLAV11AH for 900/1300lm LLAV12AH for 2000lm	WH White BK Black
Snoot LLA11SN for 900/1300lm 23SNT6 for 2000lm	WH White BK Black
Diffusion filters LLAV11 for 900/1300lm LLAV12 for 2000lm	LS Linear Spread SY Symmetrical Spread SF Soft Focus FR Frosted Etched
Color filters/gels Compatible versions provided by others for 900/1300lm ADF4 for 2000lm or Color gels provided by others	
Hex cell louver (matte black) LLAHCA11 for 900/1300lm AL4HC for 2000lm	






Assembly








LLAVRM Alcyon LED

Recessed Vertical Cylinder, 10W/900lm, 15W/1300lm, 21W/2000lm

900/1300lm



2000lm



LLAVRM Alcyon LED

Recessed Vertical Cylinder, 10 W / 900 lm, 15 W / 1300 lm, 21 W / 2000 lm

Features

1. **LED Board:** COB LED.
2. **Heat Sink:** Die-cast aluminum maintains LED junction temperature for minimum 50,000 hr lifetime at 70% lumen maintenance.
3. **Finishes:** Painted finishes with a baked enamel. Contains some powder coated finishes.
4. **Heat Sink Arm:** Tool-less aiming with 360° horizontal rotation, 180° vertical tilt and a pull down adjustment from flush recessed to semi-recessed for optimal performance.
5. **Trim/Housing:** One part integrated system including a seamless flange (16 ga powder coated steel), and pre-formed housing (22 ga powder coated steel), with pre-wired integral driver(s).
6. **Frame with mounting brackets:** Mounting brackets are adjustable vertically from inside of Frame-in-kit. Maximum ceiling thickness is 1 1/8". Accepts various types of mounting bars including C-channel, EMT (contractor supplied) and Lightolier mounting bars (Cat. # 1950 or 1951). For use in T-grid or sheet rock ceiling. See page 2 for overall dimensions.
7. **Junction box:** 4" x 3 1/2" x 2" ; .063" (14ga.) galvanized steel.
8. **Thermal Protector:** Meets NEC and UL requirements. Insulation must be kept 3" away from fixture sides and wiring compartments and must not be placed above fixture in a manner which will entrap heat.
9. **Luminaire Disconnect:** Power from Frame-in-kit to Trim/Housing connection with quick connect plug.
10. **Torsion Springs and Safety Springs:** Torsion Springs swivel to allow Trim/Housing to hang temporarily from one end to ease the process of making luminaire electrical connection complete. Safety Springs allow positive lock between Trim/Housing and Frame-in-kit for added security.
11. **Interchangeable Optics:** High efficiency metalized coating providing up to 98% total reflectivity for optimal light quality, beam control and punch. Reflector has lens attached which protects reflector finish and LEDs from contamination. Tool-less installation. Reflector sold separately to allow field replacement. Various combinations of beam angles could be achieved with 4 optic offerings.

Dimming

10 W / 900 lm: 0-10V dimming compatible.
15 W / 1300 lm: 0-10V dimming compatible.
21 W / 2000 lm: 0-10V dimming compatible.

Electrical

Electronic power supply
Input voltage: 120/277V, 50/60Hz
Input power:
900 lm: 10W
1300 lm: 15W
2000 lm: 21W
High power factor: >0.9
CRI: 80-85 (typical)

Labels

cULus Listed.
Suitable for damp location.
ENERGY STAR® certified (pending for 2000lm).
Accessories are not Energy Star qualified.
5 year warranty.

Accessories



Alcyon LED track lighting offers a full range of high performance accessories for tinting, coloring and shaping of the light beam. All accessories are designed to attach easily. A complete accessory consists of a size and series suffix.

Components

1. Frame-in kit
2. Trim kit
3. Reflector kit
4. Accessory holder*
5. Accessory spring*
6. Diffusion filter
7. Hex cell louver
8. Snoot
9. Aperture ring

* Accessory holder includes accessory spring (shown to left).


Diffusion/special filters

LLAV11 = 3 1/8" dia.
LLAV12 = 4 3/4" dia.

-  **LS** Linear spread lens
-  **FR** Frosted etched lens
-  **SF** Solite soft focus lens
-  **SY** Soft Focus lens

Hex cell louvers

LLAHC11 = 3 1/8" dia.
AL4HC = 4 3/4" dia.





Only available in matte black

LLAVRM Alcyon LED


Recessed Vertical Cylinder, 10 W / 900 lm, 15 W / 1300 lm, 21 W / 2000 lm

Aiming angles

L and W are the outer points where the candle power drops to 50% of the maximum. FC are the initial footcandles at the center of the beam. Data shown is for 3000K, for 2700K multiply FC by 0.91.



L Beam length
D Distance
W Beam Width
A Aiming Angle
FC Footcandles
C Distance to center beam
CBCP Center Beam Candlepower.




Frame: LLAVRM11H1120
Fixture: LLAVRMBK0130H1
Reflector: LLAV11RNS
CCT¹: 3000K
Output lumens: 935 lms
Input watts²: 10.1W
Efficacy: 92.6lm/w
CRI: 80 min
CBCP: 14,350 cd
Beam Angle: 11°
Field Angle: 21°
Report no³: 1147GFR

Narrow Spot 30° Horizontal Aiming

Distance			Beam	
D	C	F.C.	L	W
6	3.5	259	1.5	1.3
8	4.6	146	2.1	1.8
10	5.8	93	2.6	2.2
12	6.9	65	3.1	2.7

30° Horizontal Aiming

Distance			Beam	
D	C	F.C.	L	W
2	3.5	448	1.6	0.8
3	5.2	199	2.4	1.2
4	6.9	112	3.2	1.5
5	8.7	72	4.0	1.9




Frame: LLAVRM11H1120
Fixture: LLAVRMBK0130H1
Reflector: LLAV11RS
CCT¹: 3000K
Output lumens: 950 lms
Input watts²: 10.1W
Efficacy: 94.1lm/w
CRI: 80 min
CBCP: 6,154 cd
Beam Angle: 19°
Field Angle: 35°
Report no³: 1148GFR

Spot 30° Horizontal Aiming

Distance			Beam	
D	C	F.C.	L	W
6	3.5	111	2.7	2.3
8	4.6	62	3.6	3.1
10	5.8	40	4.5	3.9
12	6.9	28	5.4	4.6

30° Horizontal Aiming

Distance			Beam	
D	C	F.C.	L	W
2	3.5	192	2.9	1.3
3	5.2	85	4.4	2.0
4	6.9	48	5.8	2.7
5	8.7	31	7.3	3.3




Frame: LLAVRM11H1120
Fixture: LLAVRMBK0130H1
Reflector: LLAV11RNF
CCT¹: 3000K
Output lumens: 934 lms
Input watts²: 10.0W
Efficacy: 93.4lm/w
CRI: 80 min
CBCP: 4,069 cd
Beam Angle: 24°
Field Angle: 47°
Report no³: 1149GFR

Narrow Flood 30° Horizontal Aiming

Distance			Beam	
D	C	F.C.	L	W
6	3.5	73	3.5	2.9
8	4.6	41	4.6	3.9
10	5.8	26	5.8	4.9
12	6.9	18	6.9	5.9

30° Horizontal Aiming

Distance			Beam	
D	C	F.C.	L	W
2	3.5	127	3.9	1.7
3	5.2	57	5.9	2.6
4	6.9	32	7.9	3.4
5	8.7	20	9.8	4.3



Frame: LLAVRM11H1120
Fixture: LLAVRMBK0130H1
Reflector: LLAV11RF
CCT¹: 3000K
Output lumens: 929 lms
Input watts²: 10.0W
Efficacy: 92.9lm/w
CRI: 80 min
CBCP: 2,290 cd
Beam Angle: 36°
Field Angle: 63°
Report no³: 1150GFR

Flood 30° Horizontal Aiming

Distance			Beam	
D	C	F.C.	L	W
6	3.5	41	5.4	4.5
8	4.6	23	7.2	6.0
10	5.8	15	9.0	7.5
12	6.9	10	10.8	9.0

30° Horizontal Aiming



Distance			Beam	
D	C	F.C.	L	W
2	3.5	72	7.6	2.6
3	5.2	32	11.4	3.9
4	6.9	18	15.2	5.2
5	8.7	11	19.0	6.5

LLAVRM Alcyon LED


Recessed Vertical Cylinder, 10 W / 900 lm, 15 W / 1300 lm, 21 W / 2000 lm

Aiming angles

L and W are the outer points where the candle power drops to 50% of the maximum. FC are the initial footcandles at the center of the beam. Data shown is for 3000K, for 2700K multiply FC by 0.91.



L Beam length
D Distance
W Beam Width
A Aiming Angle
FC Footcandles
C Distance to center beam
CBCP Center Beam Candlepower.




Frame: LLAVRM11H1120
Fixture: LLAVRMBK1130H1
Reflector: LLAV11RNS
CCT¹: 3000K
Output lumens: 1310 lms
Input watts²: 14.8 W
Efficacy: 88.5 lm/w
CRI: 80 min
CBCP: 20,131 cd
Beam Angle: 11°
Field Angle: 21°
Report no³: 1146GFR

Narrow Spot 30° Horizontal Aiming

Distance		Beam		
D	C	F.C.	L	W
6	3.5	363	1.5	1.3
8	4.6	204	2.1	1.8
10	5.8	131	2.6	2.2
12	6.9	91	3.1	2.7

30° Horizontal Aiming

Distance		Beam		
D	C	F.C.	L	W
2	3.5	629	1.6	0.8
3	5.2	280	2.4	1.2
4	6.9	157	3.2	1.5
5	8.7	101	4.0	1.9




Frame: LLAVRM11H1120
Fixture: LLAVRMBK1130H1
Reflector: LLAV11RS
CCT¹: 3000K
Output lumens: 1320 lms
Input watts²: 14.8 W
Efficacy: 89.2 lm/w
CRI: 80 min
CBCP: 8,637 cd
Beam Angle: 19°
Field Angle: 35°
Report no³: 1145GFR

Spot 30° Horizontal Aiming

Distance		Beam		
D	C	F.C.	L	W
6	3.5	156	2.7	2.3
8	4.6	88	3.6	3.1
10	5.8	56	4.5	3.9
12	6.9	39	5.4	4.6

30° Horizontal Aiming

Distance		Beam		
D	C	F.C.	L	W
2	3.5	270	2.9	1.3
3	5.2	120	4.4	2.0
4	6.9	67	5.8	2.7
5	8.7	43	7.3	3.3




Frame: LLAVRM11H1120
Fixture: LLAVRMBK1130H1
Reflector: LLAV11RNF
CCT¹: 3000K
Output lumens: 1313 lms
Input watts²: 14.8 W
Efficacy: 88.7 lm/w
CRI: 80 min
CBCP: 5,712 cd
Beam Angle: 24°
Field Angle: 47°
Report no³: 1144GFR

Narrow Flood 30° Horizontal Aiming

Distance		Beam		
D	C	F.C.	L	W
6	3.5	103	3.5	2.9
8	4.6	58	4.6	3.9
10	5.8	37	5.8	4.9
12	6.9	26	6.9	5.9

30° Horizontal Aiming

Distance		Beam		
D	C	F.C.	L	W
2	3.5	179	3.9	1.7
3	5.2	79	5.9	2.6
4	6.9	45	7.9	3.4
5	8.7	29	9.8	4.3



Frame: LLAVRM11H1120
Fixture: LLAVRMBK1130H1
Reflector: LLAV11RF
CCT¹: 3000K
Output lumens: 1298 lms
Input watts²: 14.8 W
Efficacy: 87.7 lm/w
CRI: 80 min
CBCP: 3,209 cd
Beam Angle: 36°
Field Angle: 63°
Report no³: 1143GFR

Flood 30° Horizontal Aiming

Distance		Beam		
D	C	F.C.	L	W
6	3.5	58	5.4	4.5
8	4.6	33	7.2	6.0
10	5.8	21	9.0	7.5
12	6.9	14	10.8	9.0

30° Horizontal Aiming



Distance		Beam		
D	C	F.C.	L	W
2	3.5	100	7.6	2.6
3	5.2	45	11.4	3.9
4	6.9	25	15.2	5.2
5	8.7	16	19.0	6.5

LLAVRM Alcyon LED


Recessed Vertical Cylinder, 10 W / 900 lm, 15 W / 1300 lm, 21 W / 2000 lm

Aiming angles

L and W are the outer points where the candle power drops to 50% of the maximum. FC are the initial footcandles at the center of the beam. Data shown is for 3000K, for 2700K multiply FC by 0.91.



L Beam length
D Distance
W Beam Width
A Aiming Angle
FC Footcandles
C Distance to center beam
CBCP Center Beam Candlepower.



Frame: –
Fixture: LLAVRMBK12830H1
Reflector: LLAV12RNS

CCT¹: 3000K
Output lumens: 2247 lms
Input watts²: 21.4W
Efficacy: 105.0lm/w
CRI: 80min
CBCP: 31,716cd
Beam Angle: 11°
Report no³: 1221GFR


Narrow Spot

30° Horizontal Aiming

Distance		Beam		
D	C	F.C.	L	W
6	3.5	572	1.5	1.3
8	4.6	322	2.1	1.8
10	5.8	206	2.6	2.2
12	6.9	143	3.1	2.7

30° Vertical Aiming

Distance		Beam		
D	C	F.C.	L	W
2	3.5	991	1.6	0.8
3	5.2	441	2.4	1.2
4	6.9	248	3.2	1.5
5	8.7	159	4.0	1.9



Frame: –
Fixture: LLAVRMBK12830H1
Reflector: LLAV12RS

CCT¹: 3000K
Output lumens: 2241 lms
Input watts²: 21.3W
Efficacy: 105.2lm/w
CRI: 80min
CBCP: 15,592cd
Beam Angle: 18°
Report no³: 1220GFR


Spot

30° Horizontal Aiming

Distance		Beam		
D	C	F.C.	L	W
6	3.5	281	2.6	2.2
8	4.6	158	3.4	2.9
10	5.8	101	4.3	3.7
12	6.9	70	5.1	4.4

30° Vertical Aiming

Distance		Beam		
D	C	F.C.	L	W
2	3.5	487	2.7	1.3
3	5.2	217	4.1	1.9
4	6.9	122	5.5	2.5
5	8.7	78	6.9	3.2



Frame: –
Fixture: LLAVRMBK12830H1
Reflector: LLAV12RNF

CCT¹: 3000K
Output lumens: 2245 lms
Input watts²: 21.4W
Efficacy: 104.9lm/w
CRI: 80min
CBCP: 9,403cd
Beam Angle: 24°
Report no³: 1219GFR


Narrow Flood

30° Horizontal Aiming

Distance		Beam		
D	C	F.C.	L	W
6	3.5	170	3.5	2.9
8	4.6	95	4.6	3.9
10	5.8	61	5.8	4.9
12	6.9	42	6.9	5.9

30° Vertical Aiming

Distance		Beam		
D	C	F.C.	L	W
2	3.5	294	3.9	1.7
3	5.2	131	5.9	2.6
4	6.9	73	7.9	3.4
5	8.7	47	9.8	4.3



Frame: –
Fixture: LLAVRMBK12830H1
Reflector: LLAV12RF

CCT¹: 3000K
Output lumens: 2220 lms
Input watts²: 21.3W
Efficacy: 104.2lm/w
CRI: 80min
CBCP: 5,368cd
Beam Angle: 36°
Report no³: 1218GFR

Flood

30° Horizontal Aiming

Distance		Beam		
D	C	F.C.	L	W
6	3.5	97	5.4	4.5
8	4.6	54	7.2	6.0
10	5.8	35	9.0	7.5
12	6.9	24	10.8	9.0

30° Vertical Aiming

Distance		Beam		
D	C	F.C.	L	W
2	3.5	168	7.6	2.6
3	5.2	75	11.4	3.9
4	6.9	42	15.2	5.2
5	8.7	27	19.0	6.5

© 2017 Philips Lighting Holding B.V. All rights reserved.
Philips reserves the right to make changes in specifications and/or to discontinue any product at any time without notice or obligation and will not be liable for any consequences resulting from the use of this publication.
philips.com/luminaires



Philips Lighting North America Corporation
200 Franklin Square Drive, Somerset, NJ 08873
Tel. 855-486-2216

Philips Lighting Canada Ltd.
281 Hillmount Rd, Markham, ON, Canada L6C 2S3
Tel. 800-668-9008