


Urban

Wrap

138-4 Base

Project:	
Location:	
Cat.No:	
Туре:	
Lamps:	Qty:
Notes:	



Ordering Guide

Example: 138-4 ABS

Product Code	138-4	Wrap Base
Finish	ABS ACP ARD ASI BLK BRN BRZ FGN GRA IIN RBZ SRT VBZ VCP VGN VTC WBZ	Antique Brass Antique Copper Antique Red Antique Silver Black Brown Bronze Forest Green Granite Ironstone Rustic Bronze Shadow Rust Verde Bronze Verde Copper Verde Vintage Copper Weathered
	WHT	Bronze White

Specifications

CONSTRUCTION:

Two piece decorative wrap around base. Base can be used with any 4" dia. post.

FINISH

Resilient TGIC thermoset polyester powdercoat paint is electrostatically applied to every fixture. Specially formulated for Philips Outdoor Lighting, it provides UV protection, and the highest temperature rating in the industry. In addition to the standard color choices shown, a spectrum of custom colors is available.

Height:

17 1/8"

Width: 8 5/8"

