


PHILIPS


CoreLine Panel NOC

RC125B/RC126B









	Driver	P (W)	L x W x H (mm)	Lumen (lm)	CCT (K)	IK02	kg
RC125B	PSU	36	597 x 597 x 42.5	3400 3600	3000 4000	•	4.1
RC126B	PSU	36	622 x 622 x 42.5	3400 3600	3000 4000	•	4.3

Optional:




The luminaire shall, under no circumstance, be covered with thermal insulation matting or similar material





Inrush current



PSU	
Electrical characteristics	
I _{max} (A)	6
T _{ref} (μs)	55
MCB	No. of driver max.
B-10 A	25
B-16 A	40
C-10 A	42
C-16 A	68

