



EU Declaration of Conformity

We, Philips Lighting

I.B.R.S./C.C.R.I. /Numéro 10461
5600 VB Eindhoven, The Netherlands

Internal Ref. Nr.: 80.b

Year in which CE Mark was first affixed:
2009

Declare under our responsibility for the product(s):

Product Range:	NAME: TCW215, TCW216 Pacific Waterproof DESCRIPTION: TL based fixed general purpose luminaire
Product Code:	See Annex I

The designated product(s) is (are) in conformity with the essential requirements of the following European Directives and harmonized standards:

Low Voltage Directive (LVD), 2014/35/EU

- EN 60598-1: 2015 Luminaires – General requirements and tests
- EN 60598-2-1:1989 Luminaires – Particular requirements – Fixed general purpose luminaires
- EN 60598-2-24:2013 Luminaires – Particular requirements – Luminaires with limited surface temperatures* (only for luminaire with electronic ballast and label D= HF)
- EN 62262:2002 Degrees of protection provided by enclosures for electrical equipment against external mechanical impacts (IK code)

Electromagnetic compatibility Directive (EMC), 2014/30/EU

- EN 55015:2013 Limits and methods of measurement of radio disturbance characteristics of electrical lighting and similar equipment
- EN 61000-3-2:2014 Limits for Harmonic emissions (<16A per phase)
- EN 61000-3-3:2013 Limits. (Limitation of voltage changes, voltage fluctuations and flicker in public low-voltage supply systems, for equipment with rated current ≤ 16 A per phase and not subject to conditional connection)
- EN 61547:2009 Equipment for general lighting purposes – EMC immunity requirements

EcoDesign requirements for energy-related products Directive (ErP), 2009/125/EC and applicable Implementing Measures

- Implementing Measure EC/1194/2012

Restriction of the use of certain Hazardous Substances in electrical and electronic equipment Directive (RoHS), 2011/65/EU

- EN50581:2012

and are produced under a quality scheme at least in conformity with ISO 9001 or CENELEC permanent documents.

Sep 9th, 2016

Eindhoven
The Netherlands



John Elen

Quality Manager
Outsourced Operations
BG Professional Europe
Philips Lighting

Philips Lighting



EU Declaration of Conformity Annex I

We, Philips Lighting

I.B.R.S./C.C.R.I. /Numéro 10461

5600 VB Eindhoven, The Netherlands

Declare under our responsibility for the product(s):

Internal Ref. Nr.: 80.1a

Year in which CE Mark was first affixed: 2009

Annex I

Product range: TCW215, TCW216

Product code	Designation code
9104 026 02318	TCW215 2xTL-D58W HFS PI
9104 026 02218	TCW215 1xTL-D58W HFS PI
9104 026 01818	TCW215 1xTL-D18W HFS PI
9104 026 01918	TCW215 2xTL-D18W HFS PI
9104 026 02118	TCW215 2xTL-D36W HFS PI
9104 026 18418	TCW215 1xTL-D36W HFS TW3 PI
9104 026 18618	TCW215 1xTL-D58W HFS TW3 PI
9104 026 04618	TCW215 1xTL-D36W HFR PI
9104 026 04718	TCW215 2xTL-D36W HFR PI
9104 026 04818	TCW215 1xTL-D58W HFR PI
9104 026 02018	TCW215 1xTL-D36W HFS PI
9104 026 19318	TCW215 1xTL-D18W HFS DE PI
9104 026 19418	TCW215 2xTL-D18W HFS DE PI
9104 026 19518	TCW215 1xTL-D36W HFS DE PI
9104 026 19618	TCW215 2xTL-D36W HFS DE PI
9104 026 19818	TCW215 2xTL-D58W HFS DE PI
9104 026 19718	TCW215 1xTL-D58W HFS DE PI
9104 026 16918	TCW215 1xTL-D36W HFR TW3 PI
9104 026 18518	TCW215 2xTL-D36W HFS TW3 PI
9104 026 18718	TCW215 2xTL-D58W HFS TW3 PI
9104 026 04918	TCW215 2xTL-D58W HFR PI
9105 027 37218	TCW215 1xTL-D36W/840 HFS KIT
9105 027 37818	TCW215 1xTL-D58W/840 HFS KIT
9105 027 38418	TCW215 2xTL-D36W/840 HFS KIT
9105 027 39018	TCW215 2xTL-D58W/840 HFS KIT
9105 027 65718	TCW215 1xTL-D58W/840 HFS TW1-10A KIT
9105 027 65818	TCW215 2xTL-D36W/840 HFS TW1-10A KIT
9105 027 65918	TCW215 2xTL-D58W/840 HFS TW1-10A KIT
9105 027 65618	TCW215 1xTL-D36W/840 HFS TW1-10A KIT
9105 033 78718	TCW215 1xTL-D-XE58W/840 HFS TW1-10A KIT
9105 033 78618	TCW215 2xTL-D-XE58W/840 HFS TW1-10A KIT
9105 033 93918	TCW215 1xTL5-54W/840 HFS KIT
9105 033 94118	TCW215 2xTL5-49W/840 HFS KIT
9105 033 94618	TCW215 2xTL-D36W/840 HFS KIT AD
9105 033 94718	TCW215 2xTL-D58W/840 HFS KIT AD
9105 033 96018	TCW215 2xTL-D36W HFS PI LOC-VP
9105 033 96218	TCW215 2xTL-D58W HFS PI LOC-VP
9105 033 95918	TCW215 1xTL-D36W HFS PI LOC-VP
9105 033 96118	TCW215 1xTL-D58W HFS PI LOC-VP
9104 026 05218	TCW216 1xTL-D36W IC PI
9104 026 07318	TCW216 2xTL-D58W HFS PI
9104 026 06818	TCW216 1xTL-D18W HFS PI
9104 026 06918	TCW216 2xTL-D18W HFS PI
9104 026 07018	TCW216 1xTL-D36W HFS PI
9104 026 07118	TCW216 2xTL-D36W HFS PI

Philips Lighting



EU Declaration of Conformity Annex I

We, Philips Lighting

I.B.R.S./C.C.R.I. /Numéro 10461

5600 VB Eindhoven, The Netherlands

Internal Ref. Nr.: 80.1a

Year in which CE Mark was first affixed: 2009

Annex I

Declare under our responsibility for the product(s):

Product range: TCW215, TCW216

9104 026 07218	TCW216 1xTL-D58W HFS PI
9104 026 10818	TCW216 1xTL-D18W/840 HFS SI
9104 026 11018	TCW216 1xTL-D36W/840 HFS SI
9104 026 11318	TCW216 2xTL-D58W/840 HFS SI
9104 026 05318	TCW216 2xTL-D36W IC PI
9104 026 11418	TCW216 1xTL-D36W HFR PI
9104 026 11618	TCW216 1xTL-D58W HFR PI
9104 026 11718	TCW216 2xTL-D58W HFR PI
9104 026 17118	TCW216 2xTL5-49W HFS PI
9104 026 15618	TCW216 1xTL-D18W HFP H2L EL1 PI
9104 026 15718	TCW216 2xTL-D18W HFP EL1 PI
9104 026 15918	TCW216 2xTL-D36W HFS EL1 PI
9104 026 16018	TCW216 1xTL-D58W HFS EL1 PI
9104 026 10918	TCW216 2xTL-D18W/840 HFS SI
9104 026 17418	TCW216 1xTL-D18W HFS DE PI
9104 026 17518	TCW216 2xTL-D18W HFS DE PI
9104 026 17718	TCW216 2xTL-D36W HFS DE PI
9104 026 15818	TCW216 1xTL-D36W HFS EL1 PI
9104 026 17618	TCW216 1xTL-D36W HFS DE PI
9104 026 16318	TCW216 1xTL5-49W HFS EL3 PI
9104 026 23718	TCW216 2xTL-D36W HFS TW3 PI
9104 026 23818	TCW216 1xTL-D58W HFS TW3 PI
9104 026 23918	TCW216 2xTL-D58W HFS TW3 PI
9104 026 11518	TCW216 2xTL-D36W HFR PI
9104 026 16118	TCW216 2xTL-D58W HFS EL1 PI
9104 026 42718	TCW216 2xTL5-49W/840 HFS EL3 PI
9104 026 17918	TCW216 2xTL-D58W HFS DE PI
9104 026 11118	TCW216 2xTL-D36W/840 HFS SI
9104 026 11218	TCW216 1xTL-D58W/840 HFS SI
9104 026 23618	TCW216 1xTL-D36W HFS TW3 PI
9105 027 39618	TCW216 1xTL-D36W/840 HFS KIT
9105 027 40218	TCW216 1xTL-D58W/840 HFS KIT
9105 027 40818	TCW216 2xTL-D36W/840 HFS KIT
9105 027 41418	TCW216 2xTL-D58W/840 HFS KIT
9105 027 43918	TCW216 1xTL-D18W HFS PI IT
9105 027 44018	TCW216 2xTL-D18W HFS PI IT
9105 027 44118	TCW216 1xTL-D36W HFS PI IT
9105 027 44218	TCW216 2xTL-D36W HFS PI IT
9105 027 44318	TCW216 1xTL-D58W HFS PI IT
9105 027 44418	TCW216 2xTL-D58W HFS PI IT
9105 027 44918	TCW216 1xTL5-49W HFS PI IT
9104 026 17018	TCW216 1xTL5-49W HFS PI
9105 027 45018	TCW216 2xTL5-49W HFS PI IT
9105 027 64818	TCW216 1xTL-D36W/840 HFS TW1-10A KIT
9105 027 65018	TCW216 2xTL-D36W/840 HFS TW1-10A KIT
9105 027 65118	TCW216 2xTL-D58W/840 HFS TW1-10A KIT
9105 027 64918	TCW216 1xTL-D58W/840 HFS TW1-10A KIT

Philips Lighting



EU Declaration of Conformity Annex I

We, Philips Lighting

I.B.R.S./C.C.R.I. /Numéro 10461

5600 VB Eindhoven, The Netherlands

Internal Ref. Nr.: 80.1a

Year in which CE Mark was first affixed: 2009

Annex I

Declare under our responsibility for the product(s):

Product range: TCW215, TCW216

9105 027 70018	TCW216 1xTL-D-XA58W/840 HFS KIT
9105 027 70118	TCW216 2xTL-D-XA58W/840 HFS KIT
9104 026 17818	TCW216 1xTL-D58W HFS DE PI
9105 027 83418	TCW216 1xTL-D36W HFS PI Z2G/22D-C3
9105 027 83518	TCW216 2xTL-D36W HFS PI Z2G/22D-C3
9105 027 83618	TCW216 1xTL-D58W HFS PI Z2G/22D-C3
9105 027 83718	TCW216 2xTL-D58W HFS PI Z2G/22D-C3
9105 027 87618	TCW216 1xTL-D58W/830 HFS TW1-10A KIT
9105 027 99418	TCW216 1xTL5-49W/840 HFS SI
9105 027 98418	TCW216 2xTL5-49W/840 HFS PI
9105 027 98618	TCW216 1xTL5-49W/840 HFS EL3 PI
9105 027 98718	TCW216 2xTL5-49W HFS TW3 PI
9105 033 03418	TCW216 2xTL-D36W/840 HFS EL3 SI
9105 033 03518	TCW216 2xTL-D58W/840 HFS EL3 SI
9105 033 28518	TCW216 2xTL-D18W HFP EL3 PI
9105 033 30118	TCW216 1xTL-D58W HFS H2L WB TW3 PI
9105 033 30218	TCW216 1xTL-D58W HFS H2L NB TW3 PI
9105 033 30318	TCW216 1xTL-D58W HFS H2L A TW3 PI
9105 033 41118	TCW216 1xTL5-49W/840 HFS KIT
9105 033 41218	TCW216 2xTL5-49W/840 HFS KIT
9105 033 41318	TCW216 2xTL5-28W/840 HFS KIT
9105 033 41418	TCW216 2xTL5-49W/840 HFS H1L KIT
9105 033 41618	TCW216 1xTL5-49W/840 HFS H2L WB KIT
9105 033 41718	TCW216 1xTL5-49W/840 HFS H2L NB KIT
9105 033 41818	TCW216 1xTL5-49W/840 HFS H2L A KIT
9105 033 41518	TCW216 3xTL5-49W/840 HFS H2L KIT
9105 033 41918	TCW216 2xTL-D-XE58W/840 HFP-XT KIT
9105 033 42018	TCW216 2xTL-D-XAP58W/840 HFS KIT
9105 033 42118	TCW216 1xTL-D-XAP58W/840 HFS H2L NB KIT
9105 033 78218	TCW216 2xTL5-35W HFS PI
9105 033 78418	TCW216 2xTL5-49W/840 HFS TW1-10A KIT
9105 033 78818	TCW216 1xTL5-14W/840 HFS SI
9105 033 79018	TCW216 2xTL-D36W HFS EL3 PI
9105 033 79218	TCW216 2xTL5-28W HFS PI
9105 033 79418	TCW216 1xTL-D58W HFS EL3 PI
9105 033 79518	TCW216 1xTL5-28W/840 HFS SI
9105 033 79618	TCW216 2xTL-D58W HFS EL3 PI
9105 033 79718	TCW216 2xTL5-28W/840 HFS SI
9105 033 77618	TCW216 1xTL5-35W HFS PI
9105 033 79918	TCW216 2xTL5-35W/840 HFS PI
9105 033 80118	TCW216 1xTL-D36W HFS EL3 PI
9105 033 80218	TCW216 1xTL5-28W/840 HFS H2L EL3 SI
9105 033 80318	TCW216 1xTL5-35W/840 HFS EL3
9105 033 77918	TCW216 1xTL-D58W/830 HFS KIT
9105 033 78018	TCW216 1xTL5-35W/840 HFS PI
9105 033 86218	TCW216 1xTL5-28W HFS PI
9105 033 86318	TCW216 1xTL5-54W HFS PI

Philips Lighting



EU Declaration of Conformity Annex I

We, Philips Lighting

I.B.R.S./C.C.R.I. /Numéro 10461

5600 VB Eindhoven, The Netherlands

Internal Ref. Nr.: 80.1a

Year in which CE Mark was first affixed: 2009

Annex I

Declare under our responsibility for the product(s):

Product range: TCW215, TCW216

9105 033 86418	TCW216 2xTL5-54W HFS PI
9105 033 86618	TCW216 1xTL5-35W/840 HFS KIT
9105 033 86718	TCW216 2xTL5-35W/840 HFS KIT
9105 033 86818	TCW216 1xTL5-54W/840 HFS KIT
9105 033 86918	TCW216 2xTL5-54W/840 HFS KIT
9105 033 87018	TCW216 1xTL5-49W/840 HFS TW1-10A KIT
9105 033 90518	TCW216 1xTL5-54W/840 HFS PI
9105 033 91118	TCW216 2xTL5-49W/840 HFR PI
9105 033 78918	TCW216 2xTL5-54W/840 HFS PI
9105 033 86518	TCW216 1xTL5-28W/840 HFS KIT
9105 033 93618	TCW216 1xTL5-35W/840 HFS TW1-10A KIT
9105 033 94818	TCW216 1xTL-D36W/840 HFS FU KIT AD
9105 033 95018	TCW216 2xTL-D36W/840 HFS FU KIT AD
9105 033 95118	TCW216 2xTL-D58W/840 HFS FU KIT AD
9105 033 94918	TCW216 1xTL-D58W/840 HFS FU KIT AD
9105 033 97818	TCW216 2xTL5-35W/840 HFS EL3 PI
9105 044 16718	TCW216 2xTL5-49W HFR-TD PI
9105 044 16218	TCW216 2xTL5-54W/840 HFS EL1 PI
9105 044 16118	TCW216 1xTL5-54W/830 HFS KIT
9105 044 17618	TCW216 2xTL5-28W/840 HFR-TD KIT2
9105 044 17318	TCW216 1xTL5-28W/830 HFS KIT
9105 027 84018	TCW216 1xTL5-49W/840 HFS PI

Sep 9th, 2016

Eindhoven

The Netherlands

John Elen

Quality Manager

Outsourced Operations

BG Professional Europe

Philips Lighting