



PHILIPS

TrueLine


SM530C



Surface Mounted					Sensor/ Blind sensor holder.		
		A	B	C	D		
Standalone	L1130	1130	759	200	171	3.2	
	L1170	1170			211	•	3.4
	L1410	1409	1031		178		3.8
	L1450	1449			219	•	4.1
Line End	L1130	1128	759	200	170	3.2	
	L1170	1168			210	•	3.4
	L1410	1408	1031		177		3.8
	L1450	1448			217	•	4.1
Line Feature	L1130	1127	759		170	3.2	
	L1170	1167			210	•	3.4
	L1410	1406	1031		177		3.8
	L1450	1446			217	•	4.1


Surface Mounted

Dimensions in mm







DALI Standalone / Line End




1







2a




2b




2c



3





4a



4b






Push-in (PIP) PSD PI-5 Line End / Line Feature




5a


PI-7 Line End / Line Feature




5b



6a




6b



6c




Cover remover (ZZS400 OCR)




Replace 6a, b, c,



ACL versions only



Inrush current



I _{max} (A)	19
T _{ref} (μs)	280
Condition: Input voltage 220V	
MCB	Luminaires Max.
B-10A	15
B-13A	19
B-16A	24
B-20A	30
C-25A	37
C-10A	24
C-13A	32
C-16A	40
C-20A	49
C-25A	62



© 2016 Philips Lighting Holding B.V.

All rights reserved. Reproduction in whole or in part is prohibited without the prior written consent of the copyright owner. The information presented in this document does not form part of any quotation or contract, is believed to be accurate and reliable and may be changed without notice. No liability will be accepted by the publisher for any consequence of its use. Publication thereof does not convey nor imply any license under patent- or other industrial or intellectual property rights.

Philips Lighting Holding B.V.
The Netherlands