

6000 lm/4ft w/ 100% Down Kit\*

3000/3500/4000K






Project:
Spec Type:
Catalog No: 24x5LxBAJ
Qty
Line Notes:

With FloatPlane LED, it's easier than ever to integrate sleek and sporty style into your layout and within budget. Fresh and playful, with Curve and Edge profile options, FloatPlane's performance rivals that of high-end LED luminaires with the affordability of fluorescent. Available tunable white technology gives you the ability to vary color temperature and intensity, harmonizing lighting with your daily life.

## **Ordering guide**



# Mount Type Consult separate mounting spec sheet for mount type options Suspension Length Distance from ceiling to top of luminaire in inches Options & Integrated Controls Please indicate with check mark. Dust Cover Response Daylight Single Zone (DS) SpaceWise DT Occupancy & Daylight Sensor (SZ)



<sup>\*</sup> Nominal values within a range. Down kits and dust covers reduce output & efficacy. Consult photometry data for color temp, lumens & distribution of chosen configuration.

<sup>†</sup> Not all wiring types are available with all configurations. Consult Philips Ledalite for a complete list of available options.

6000 lm/4ft w/ 100% Down Kit\* 3000/3500/4000K

#### **Optical System**

White light emitted from dual linear arrays of lateral-facing LEDs is diffused and redirected into the upper and lower hemispheres with a combination of high reflectivity elements and acrylic diffusers. This delivers a highly efficient 70% up / 30% down indirect/direct distribution with a wide, homogeneous batwing distribution in the upper hemisphere. Twin polymer diffusers on the lower surface combine for an optical aperture of 5-1/2" to deliver a uniform, controlled brightness, maximizing visual comfort and luminaire efficacy. Factory or field installable variable optics kits are available to modify the distribution to 75% down or close to 100% down light. Field installable dust covers available on suspended versions.

#### **Endcaps**

Diecast aluminum endcaps in either Edge or Curve versions to match housing.

#### **Finish**

High quality powder coated, available in matte white, black or titanium silver. Other custom colors, including Pacific Aqua and Surf Yellow, available on request. White sensors only.

#### Housing

Precision formed 18 gauge cold-rolled steel. Approx. cross section size: 1.5"h x 8"w (suspended) or 5.7"w (wall mount).

#### Weight

Maximum: Suspended 3.5lb/ft, Wall 3.3lb/ft

## **Electrical**

Factory pre-wired to section ends with quick-wire connectors

#### **Standard Drivers**

Philips Advance Xitanium 0-10V, 1-100%. Philips Advance Xitanium SR, 5-100% (for SpaceWise DT).

Class 2 rated output. Consult Philips Ledalite for other available drivers.

#### **Standard Battery Pack**

Philips Bodine, 90 min, 10W, Class 2 rated output, Emergency lumen output = 10W x luminaire efficacy x 1.1. Typical output 1400lm.

#### **Lumen Maintenance**

LEDs have been tested by the manufacturer in accordance with IESNA LM-80-08. At an ambient temperature of 25°C, the LED lumen maintenance expectation according to IES TM-21-11 is: L<sub>80</sub> (12k) 70,000 hrs suspended / 64,000 hrs wall. (Reported methodology) L<sub>70</sub> (12k) 108,000 hrs suspended / 98,000 hrs wall. (Projected methodology)

#### **Source Color**

LEDs rated for color rendering CRI >80, R9 >0 and fixture to fixture color accuracy within 2 SDCM.

#### Controls

Suspended version available with the following integrated controls:
Response daylight sensor (for single zone).
SpaceWise DT occupancy & daylight sensor w/ advanced grouping & dwell time.
SpaceWise DT commissioning via Android phone and Philips Field App. Compatible dimming wireless wall switches are available. For more information, please refer to www.philips.com/spacewise

#### Mounting

Suspended: Rapid installation sling mount at joints and ends. High strength aircraft cable and stainless steel gripper provide unlimited vertical adjustment and are independently tested to stringent safety standards. Wall: A hidden steel rail and bracket system attaches to the existing structure and supports housings close to the wall. Mount positioning is fully variable along the modules to accommodate site conditions, spaced up to 4½' on center and within 12" of an end or joint.

#### loints

Self-aligning, gasketed joining system. Access panels in the driver channel allow quick and hassle-free wiring of modules either before or after mechanical joints are completed.

#### **Approvals**

Certified to UL, CSA and IES standards. Certain suspended versions (24x5L) are DesignLights Consortium® qualified. Please see the DLC QPL list for exact catalog numbers (www.designlights.org/QPL).

#### Warranty


Philips indoor professional luminaires 5 year LED warranty: http://www.philips.com/warranties


#### **Environment**

Rated for dry or damp locations in operating ambient temperatures 0-40°C (32-104°F). Certain luminaire components may be adversely affected by contaminants. Damage caused by sulfur, chlorine, petroleum based solutions or other contaminants in the area of operation are not covered under warranty. Not suitable for natatorium environments.

Due to continuing product improvements, Philips Ledalite reserves the right to change the specifications without notice.


#### **Dimensions - Cross Section**






6000 lm/4ft w/ 100% Down Kit\* 3000/3500/4000K

# **Dimensions - Modules**




# **Optics and Styles**




6000 lm/4ft w/ 100% Down Kit\* 3000/3500/4000K

## Photometry - 3500K



1% Up / 99% Down



#### Candela Distribution

Vertical		Hor	izontal A	ngle		Zonal
Angle	0	22.5	45	67.5	90	Lumens
0	1640	1640	1640	1640	1640	0
5	1635	1635	1635	1635	1633	155
15	1588	1578	1582	1582	1574	446
25	1481	1471	1477	1473	1467	679
35	1323	1314	1319	1312	1306	822
45	1125	1115	1117	1107	1107	859
55	883	878	876	868	868	781
65	613	609	603	597	597	597
75	327	321	319	317	317	339
85	72	76	80	82	82	93
90	0	0	0	0	0	0
95	4	2	0	0	0	1
105	6	4	4	2	2	4
115	6	8	6	4	4	6
125	8	8	8	6	6	7
135	10	10	10	8	8	7
145	12	10	10	10	8	6
155	12	10	10	8	8	4
165	10	10	10	10	10	3
175	10	10	8	8	8	1
180	10	10	10	10	10	0

Photometry based on 4ft white luminaire. Dust covers and non-white finishes reduce delivered lumens. Custom color finishes may shift output color temperature.

Fixture photometry has been conducted in accordance with IESNA LM-79-08

IES files for this and other photometric options can be downloaded online at www.lightingproducts.philips.com

#### Coefficients of Utilization (%)

RCR	Ceiling:		8	0			70			50		0
KCK	Wall:	70	50	30	10	70	50	30	50	30	10	0
0		119	119	119	119	116	116	116	111	111	111	99
1		108	104	99	95	106	101	97	97	94	91	83
2		98	90	83	77	96	88	82	84	79	75	69
3		90	79	71	64	87	77	70	74	68	62	58
4		82	70	61	54	80	69	60	66	59	53	49
5		75	62	53	47	73	61	53	59	51	46	42
6		70	56	47	41	68	55	47	53	46	40	37
7		64	51	42	36	63	50	42	48	41	35	33
8		60	46	38	32	58	46	37	44	37	31	29
9		56	42	34	29	55	42	34	41	33	28	26
10		52	39	31	26	51	39	31	38	31	26	24

#### Avg. Luminance (cd/m2)

Vertical Angle	0 Ho	orizontal Ang 45	gle 90
55	7573	7506	7440
65	7131	7018	6950
75	6211	6063	6026
85	4062	4501	4611

#### Distribution

Hemisphere	1% Up / 99% Down		
Spacing Along (0 °)	1.27		
Spacing Across (90 °)	1.26		

6000 lm/4ft w/ 100% Down Kit\* 3000/3500/4000K

## **Optical Performance**


Nominal CCT:	3000K	3500K	4000K
Flux (lm)	4711	4809	4844
Efficacy (lm/W)	94.6	96.6	97.3
Power (W)	49.8	49.8	49.8
CCT (K)	3032	3344	3907
CRI	81	82	83
R9	2	5	10
x	0.4376	0.4178	0.3867
у	0.4093	0.4036	0.3864
Duv	0.0020	0.0030	0.0030

## **Electrical Performance - 3500K**

Input Voltage	120V	277V	347V	
Input Power	49.8W	49.2W	41.8W	
Input Current	0.42A	0.18A	0.12A	
Power Factor	0.998	0.963	0.976	
Total Harm. Distortion	6.5%	13.4%	9.0%	

Tested values . contact technical support for rated values. Off-state power zero unless certain controls are specified.

With SpaceWise DT, standby power <0.5W (120V) or <0.8W (277V).





use of this publication.